

**TECHSPEC® 2X, 1064nm Vega® Nd:YAG Laser Line Beam Expander**



2X, 1064nm DA Beam Expander, #35-095

Stock #35-095 **2 In Stock**

⊖ 1 ⊕ MRP ₹35,653

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹35,653 each
Qty 10-24	₹31,721 each
Qty 25-99	₹28,313 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Beam Expander **Type:**

Fixed Magnification **Style:**

**Physical & Mechanical Properties**

Length (mm):

83.00

Weight (g):

74

Housing Diameter (mm):

29.95

## Optical Properties

Entrance Aperture (mm):

8

Exit Aperture (mm):

23

Expansion Power:

2X

Substrate:

Fused Silica (Corning 7980)

Transmission (%):

>99 (nominal)

Angle of Incidence (°):

0

Coating:

Laser V-Coat (1064nm)

Design Wavelength DWL (nm):

1064

Transmitted Wavefront, P-V:

<λ/10 for 4mm input beam (nominal, λ = DWL)

Wavelength Range (nm):

1000 - 1140

Coating Specification:

R<sub>abs</sub> <0.25% @ 1064nm

Damage Threshold, By Design:

10 J/cm<sup>2</sup> @ 1064nm, 10ns, 20Hz

Divergence Adjustment:

Rotating Optics

Damage Threshold, Pulsed:

10 J/cm<sup>2</sup> @ 1064nm, 10ns, 20Hz

## Threading & Mounting

Mounting Threads:

Input Male M30 x 1

## Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Singapore

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- AR Coated for Laser Wavelengths: 266nm, 355nm, 405nm, 532nm, 1064nm, and 1940nm
- Fixed Magnifications Available from 1.5X to 20X
- Divergence Adjustable through Rotating Optical Design

TECHSPEC® Vega® Laser Line Beam Expanders are designed for demanding laser applications including laser materials processing, medical, and research. These compact beam expanders are optimized at common laser wavelengths, including Nd:YAG wavelengths, for high performance transmitted wavefront, with designs achieving λ/10 transmitted wavefront error. To ensure compatibility with high power lasers, these beam expanders are designed to prevent ghost images from focusing on internal surfaces. TECHSPEC Vega Laser Line Beam Expanders easily mount with M30 x 1 threading and provide excellent value both for single unit purchases as well as volume integration.

**Note:** The length of these beam expanders will change upon divergence adjustment, typically by 1 to 2mm from the specified length.

TECHSPEC® Vega® Broadband Beam Expanders are also available. For more cost sensitive applications, Edmund Optics also offers TECHSPEC Scorpii® Nd:YAG Beam Expanders. For HeNe laser applications, TECHSPEC Arcturus® HeNe Beam Expanders are available. For higher precision applications where sliding optics are necessary, please see our TECHSPEC Draconis® Nd:YAG Laser Line Beam Expanders or TECHSPEC Draconis®

[Broadband Beam Expanders](#). For broadband or ultrafast applications, [TECHSPEC Canopus® Reflective Beam Expanders](#) are available.

To learn more about the difference between the 2 $\mu$ m and 2 $\mu$ m low OH<sup>-</sup> content beam expanders, along with the different types of fused silica, review our [UV vs. IR Grade Fused Silica application note](#).

532nm versions are compatible with popular 515nm laser applications, and 1064nm versions are ideal for use with laser applications at 1030nm, 1070nm, and 1080nm.

