

TECHSPEC®

2X, 532nm Scorpii® Nd:YAG Beam Expander



2X, 532nm LCht Fixed YAG Beam Expander, #37-047

Stock **#37-047** 10 TO 12 DAYS

-

1

+

₹16,008.00

ADD TO CART

Qty 1-9
₹16,008.00
Qty 10+
₹14,181.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Coating:
VIS 0° (425-675nm)

Design Wavelength DWL (nm):
532

Entrance Aperture (mm): 3.5
Exit Aperture (mm): 5.2
Expansion Power: 2X
Substrate: ☐ Optical Glass
Length (mm): 20.30
Mounting Threads: M22 x0.75
Transmission (%): >98 (nominal)
Type: Beam Expander
Weight (g): 40
Housing Diameter (mm): 29.95
Transmitted Wavefront, P-V: <λ/4 @ 532nm for Input Beam ≤2.2mm (by design)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Wavelength Range (nm): 532
Style: Fixed Magnification
Divergence Adjustment: None

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View