

## 3" x 3" Positive, USAF 1951 Hi-Resolution Target



Stock #64-862 **3 In Stock**

- 1 + MRP ₹2,22,489

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹2,22,489 each
Qty 5+	₹2,11,402 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Positive Target **Type:**

High Resolution **Options:**

#### Physical & Mechanical Properties

3 x 3 **Dimensions (inches):**

**Thickness (mm):**

1.50 ±0.05

Beveled **Edges:**

≤0.00254 **Flatness (mm):**

### Optical Properties

Vacuum Deposited Durable Chromium **Coating:**

Float Glass **Substrate:** □

≥3.0 **Optical Density OD (Average):**

Minimum: Group -2, Element 1  
Maximum: Group 9, Element 3 **Resolution:**

20-10 **Surface Quality:**

### Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

United States **Country of Origin:**


**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Negative and Positive Patterns On Glass
- Two Sizes Available
- Each is Boxed and Includes Resolution Value Chart
- High Resolution Target Available (down to 645 lp/mm)

USAF 1951 Glass Slide Resolution Test Targets are available in either positive (chrome pattern on clear background) or negative (clear pattern on a chrome background). The positive pattern is recommended for the quality control of microscopes and magnifiers. The negative pattern is ideal for collimators and other illuminated test equipment. USAF 1951 Glass Slide Resolution Test Targets are boxed and include a resolution value chart. The targets conform to ML-S-150A.

## Technical Information



Element	Group Number										For High Res only	
	-2	-1	0	1	2	3	4	5	6	7	8	9
1	0.250	0.500	1.00	2.00	4.00	8.00	16.00	32.0	64.0	128.0	256.0	512.0
2	0.280	0.561	1.12	2.24	4.49	8.98	17.95	36.0	71.8	144.0	287.0	575.0
3	0.315	0.630	1.26	2.52	5.04	10.10	20.16	40.3	80.6	161.0	323.0	645.0
4	0.353	0.707	1.41	2.83	5.66	11.30	22.62	45.3	90.5	181.0	362.0	—
5	0.397	0.793	1.59	3.17	6.35	12.70	25.39	50.8	102.0	203.0	406.0	—
6	0.445	0.891	1.78	3.56	7.13	14.30	28.50	57.0	114.0	228.0	456.0	—

Condition	Positive Test Target	Negative Test Target
Lighting Condition	Front-lit or general lighting	Back-lit or highly illuminated

<b>Appearance of Bars</b>	Dark bars on a bright background	Bright bars on a dark background
<b>Application</b>	General optical testing	High-contrast or back-lit testing
<b>Substrate</b>	Clear substrate with chrome patterns	Chrome-covered substrate with clear patterns
<b>Example Use Case</b>	Microscope calibration	Projection systems, back-lit displays

---