

[See all 19 Products in Family](#)

3 x 3 x 15mm, 1064nm SHG, Type I LBO Nonlinear Crystal



Stock **#11-173** 3 In Stock

-

1

+

₹36,900

ADD TO CART

Volume Pricing	
Qty 1+	₹36,900 each
Need More?	Request Quote

Product Downloads

General	
Nonlinear Crystal	Type:
SHG @ 1064nm, Type I	Typical Applications:
LBO	Crystal Type:
<0.1mm x45°	Protective Chamfer:
Physical & Mechanical Properties	
	Dimensions (mm):

3.0 x 3.0 +0.0/-0.1	
15.00 +0.0/-0.1	Thickness (mm):
<20	Parallelism (arcsec):
<5	Perpendicularity (arcmin):

Optical Properties	
20-10	Surface Quality:
AR Coating	Coating:
1064	Design Wavelength DWL (nm):
λ/10	Surface Flatness (P-V):
Coating Specification: S1: 532 & 1064nm AR Coating S2: 532 & 1064nm AR Coating	
Damage Threshold, By Design: ☐ 10 J/cm² @ 1064nm, 10ns, 10Hz	
Damage Threshold, Pulsed: 10 J/cm² @ 1064nm, 10ns, 10Hz	
90/11.6	Orientation Θ/Φ (°):

Threading & Mounting	
Unmounted	Mount:

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:
Israel	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- BBO Crystals for Frequency Conversion of 800nm and 1030nm Lasers
- LBO Crystals for Frequency Conversion of 1030nm and 1064nm Lasers
- High Damage Thresholds Up to 10 J/cm² @ 1064nm, 10ns, 10Hz
- Broad Transparency Range from the UV to the IR

Nonlinear Crystals of either β-barium borate (BBO) or lithium triborate (LBO) are used for frequency conversion of laser sources. BBO crystals feature thicknesses from 0.2mm to 0.5mm to minimize group velocity mismatch and are ideal for frequency doubling or tripling of Ti:Sapphire and Yb:doped laser pulses. The critical and noncritical phase matching LBO crystals are ideal for second or third harmonic generation of Nd:YAG and Yb:doped lasers. Nonlinear Crystals with 20-10 surface quality and λ/10 (LBO) or λ/8 (BBO) surface flatness provide the broad transparency range and large nonlinear coefficient needed for the harmonic generation of fundamental laser frequencies. Each crystal features a protective anti-reflection (AR) coating that minimizes reflection and limits fogging from ambient conditions.