

[See all 215 Products in Family](#)

TECHSPEC<sup>®</sup>

# 30mm Dia., 0.50 Numerical Aperture, 600-1050nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC<sup>®</sup> Precision Aspheric Lenses

Stock **#16-983-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

₹40,230

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹40,230 each                  |
| Qty 6-25       | ₹32,220 each                  |
| Qty 26-49      | ₹30,240 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Aspheric Lens

Physical & Mechanical Properties

|                                                                                                      |                                      |
|------------------------------------------------------------------------------------------------------|--------------------------------------|
| 30.00 ±0.025                                                                                         | Diameter (mm):                       |
| <3                                                                                                   | Centering (arcmin):                  |
| 27.00                                                                                                | Clear Aperture CA (mm):              |
| 6.59                                                                                                 | Edge Thickness ET (mm):              |
| 12.50 ±0.10                                                                                          | Center Thickness CT (mm):            |
| Protective as needed                                                                                 | Bevel:                               |
| Plano                                                                                                | Shape of Back Surface:               |
| Optical Properties                                                                                   |                                      |
| 30.00 @587.6nm                                                                                       | Effective Focal Length EFL (mm):     |
| 0.50                                                                                                 | Numerical Aperture NA:               |
| 22.53                                                                                                | Back Focal Length BFL (mm):          |
| N-SF5                                                                                                | Substrate: □                         |
| 0.4λ                                                                                                 | Asphere Figure Error, RMS @ 632.8nm: |
| NIR+ (600-1050nm)                                                                                    | Coating:                             |
| Coating Specification:<br>Ravg <0.5% @ 600 - 1050nm @±30° AOI<br>Rabs <1.5% @ 600 - 1050nm @±30° AOI |                                      |
| 40-20                                                                                                | Surface Quality:                     |
| 1.00                                                                                                 | f/#:                                 |
| 600 - 1050                                                                                           | Wavelength Range (nm):               |
| Infinite                                                                                             | Conjugate Distance:                  |
| Regulatory Compliance                                                                                |                                      |
| View                                                                                                 | Certificate of Conformance:          |
| Singapore                                                                                            | Country of Origin:                   |
| Edmund Optics India Private Limited                                                                  | Imported By:                         |

## Product Details

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.

## Compatible Mounts