

TECHSPEC[®] 30mm Dia., 1mm Thick, VIS 0° Coated λ /4 N-BK7 Window



Stock #23-386 5 In Stock

-

1

+

₹8,069

ADD TO CART

Volume Pricing	
Qty 1-5	₹8,069 each
Qty 6-25	₹6,455 each
Qty 26-49	₹6,088 each
Need More?	Request Quote

Product Downloads

General

Protective Window

Type:

Physical & Mechanical Properties

Protective as needed

Bevel:

90

Clear Aperture (%):

27.00	Clear Aperture CA (mm):
30.00 +0.00/-0.25	Diameter (mm):
1.00 ±0.20	Thickness (mm):
Fine Ground	Edges:
610.00	Knoop Hardness (kg/mm²):
<1	Parallelism (arcmin):
0.21	Poisson's Ratio:
82	Young's Modulus (GPa):

Optical Properties	
64.17	Abbe Number (v _d):
VS 0° (425-675nm)	Coating:
R _{avg} ≤0.4% @ 425 - 675nm	Coating Specification:
1.516	Index of Refraction (n _d):
N-BK7	Substrate:
60-40	Surface Quality:
λ/4	Transmitted Wavefront, P-V:
425 - 675	Wavelength Range (nm):
Damage Threshold, Reference: □ 5 J/cm² @ 532nm, 10ns	

Material Properties	
7.1 (-30 to +70°C) 8.3 (+20 to +300°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.51	Density (g/cm³):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Vietnam	Country of Origin:
Edmund Optics India Private Limited	Imported By:






Product Details





- Circular and Rectangular Sizes from 2mm to 200mm
- 8 Broadband Anti-Reflection Coating Options Available
- World's Largest Selection of Standard N-BK7 Windows
- Also Available with [Ultra-Thin N-BK7 Windows](#)

TECHSPEC® λ/4 N-BK7 Precision Windows are ideally suited for industrial and low-power laser applications. The high tolerance design yields minimal beam distortion and scatter. Broadband coating options extend the range of these precision windows through the visible and near-infrared spectra. TECHSPEC® λ/4 N-BK7 Precision Windows are offered in circular and rectangular sizes ranging from 2mm to 200mm.

Note: New additions to this product family may be specified with a transmitted wavefront distortion (TWD) specification instead of a surface flatness. For more information on the difference between these two specifications, see our application note on [Understanding Optical Windows](#).

Technical Information

Uncoated N-BK7 Typical Transmission 	Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra. Click Here to Download Data
N-BK7 with MgF₂ Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with MgF2 (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with VIS-EXT Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with VIS-NIR Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

	
N-BK7 with YAG-BBAR Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% \text{ @ } 532\text{nm}$ $R_{abs} \leq 0.25\% \text{ @ } 1064\text{nm}$ $R_{avg} \leq 1.0\% \text{ @ } 500 - 1100\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% \text{ @ } 600 - 1050\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\% \text{ @ } 750 - 800\text{nm}$ $R_{abs} \leq 1.0\% \text{ @ } 800 - 1550\text{nm}$ $R_{avg} \leq 0.7\% \text{ @ } 750 - 1550\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

Coating Curves

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts

