

TECHSPEC[®] 300nm CWL, 25 Dia. Hard Coated OD 4.0 25nm Bandpass Filter



Stock **#12-078** 4 In Stock

☐ [Additional Bandwidths](#)

-

1

+

₹19,852

ADD TO CART

Volume Pricing	
Qty 1-5	₹19,852 each
Qty 6-25	₹15,570 each
Qty 26-49	₹14,636 each
Need More?	Request Quote

Product Downloads

General	
Bandpass Filter	Type:
Physical & Mechanical Properties	
25.00 +0.0/-0.1	Diameter (mm):
21.0	Clear Aperture CA (mm):

Construction: Mounted in Black Anodized Ring	
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2	
Substrate Thickness (mm): 3.0 ±0.2	
Optical Properties	
Angle of Incidence (°): 0	
Bandwidth (nm): 20	
Optical Density OD (Average): ≥4.0	
Center Wavelength CWL (nm): 300.00	
Center Wavelength CWL Tolerance (nm): ±3	
Full Width-Half Max FWHM (nm): 25.00	
Full Width-Half Max FWHM Tolerance (nm): ±3	
Substrate: ☐ Fused Silica	
Minimum Transmission (%): ≥70	
Coating: Hard Coated	
Surface Quality: 80-50	
Blocking Wavelength Range (nm): 200 - 650	
Threading & Mounting	
Mount Thickness (mm): 5.0 ±0.1	
Environmental & Durability Factors	
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7	
Regulatory Compliance	
RoHS 2015: Compliant	
Certificate of Conformance: View	
Reach 247: Compliant	
Country of Origin: United States	
Imported By: Edmund Optics India Private Limited	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Ideal for Life Science Instrumentation
- High Transmission, Deep Blocking
- Used to Prevent Photobleaching in Microscopy Applications
- Hard Coated OD 4.0 [5nm](#), [10nm](#) and [50nm](#) Bandpass Filters also Available

TECHSPEC® Hard Coated OD 4.0 25nm Bandpass Filters are designed to be a midrange alternative to broadband or narrowband filters. These filters are ideal for fluorescence microscopy or other life science applications that rely

on fluorescence detection such as flow cytometry or qPCR. TECHSPEC® Hard Coated OD 4.0 25nm Bandpass Filters can also be used to eliminate unwanted background noise while enhancing the signal-to-noise ratio in imaging or machine vision applications. The filters are designed to have a 0° angle of incidence and are mounted in a black anodized ring. Hard Coated OD 4.0 **5nm**, **10nm**, and **50nm** bandpass filters are also available.

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm² @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

Technical Information



All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.