

[See all 215 Products in Family](#)

TECHSPEC® 30mm Dia., 0.66 Numerical Aperture, 350-700nm Coated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-964** **12 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ ₹35,188

ADD TO CART

Volume Pricing	
Qty 1-5	₹35,188 each
Qty 6-25	₹28,182 each
Qty 26-49	₹26,469 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

30.00 +0.00/-0.025 **Diameter (mm):**

Centering (arcmin):

<3

27.00 Clear Aperture CA (mm):

6.62 Edge Thickness ET (mm):

15.00 ±0.10 Center Thickness CT (mm):

Protective as needed Bevel:

Plano Shape of Back Surface:

Optical Properties

22.50 @ 587.6nm Effective Focal Length EFL (mm):

0.66 Numerical Aperture NA:

13.53 Back Focal Length BFL (mm):

[N-SF5](#) Substrate:

0.4λ Asphere Figure Error, RMS @ 632.8nm:

VIS-EXT+ (350-700nm) Coating:

Coating Specification:

R_{avg} <0.5% @ 350 - 700nm @ ±30° AOI

R_{abs} <1.5% @ 350 - 700nm @ ±30° AOI

40-20 Surface Quality:

0.75 f#:

350 - 700 Wavelength Range (nm):

Infinite Conjugate Distance:

44.44 Power (diopters):

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 250:

Singapore Country of Origin:

Edmund Optics India Private Limited Imported By:

Product Details

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.

Compatible Mounts