

TECHSPEC®

30mm Dia. x 120mm FL, NIR I Inked, Double-Convex Lens



Stock #63-655-INK 17 TO 22 D= DAYS

[Other Coating Options](#)

-

1

+

₹5,699.00

ADD TO CART

Qty 1-9
₹5,699.00
Qty 10+
₹5,133.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Back Focal Length BFL (mm):
118.34

Effective Focal Length EFL (mm): 120.00
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 3.17
Radius R₁=R₂ (mm): 123.17
Clear Aperture CA (mm): 29.00
f/#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View