

[See all 8 Products in Family](#)

## 30mm Dia. 1000-2000nm, NIR Linear Polarizer



Stock #48-889 **8 In Stock**

MRP ₹43,282

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹43,282 each
Qty 6-25	₹36,764 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Linear Polarizer **Type:**

### Physical & Mechanical Properties

30.00 **Diameter (mm):**

2.00 ±0.2 **Thickness (mm):**

**Parallelism (arcmin):**

<4

**Dimensional Tolerance (mm):**

+0.0/-0.2

**Construction:**

Dichroic Polarizing Film on Glass

**Optical Properties**

**Coating:**

Uncoated

**Extinction Ratio:**

1000:1

**Substrate:**

Polymer Film on [B270](#)

**Transmission (%):**

33.00

**Transmission Tolerance (%):**

±3

**Wavelength Range (nm):**

1000 - 2000

**Environmental & Durability Factors**

**Operating Temperature (°C):**

-25 to +80

**Regulatory Compliance**

**RoHS 2015:**

[Compliant](#)

**Reach 224:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Country of Origin:**

Japan

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Ideal for Fiber Optic and Laser Applications
- 750 – 850nm and 1000 – 2000nm Wavelength Ranges
- 1000:1 Extinction Ratio

These high contrast NIR Glass Linear Polarizers consist of a polymer polarization film layered between two flat pieces of optical quality glass. These polarizers are ideal for a variety of applications involving low power NIR [lasers](#), [LEDs](#), and other NIR sources. Their extended broadband range is also ideal for a variety of telecommunication devices including fiber optic isolators and couplers. NIR Glass Linear Polarizers have a 1000:1 extinction ratio. The high contrast polarizers are available in diameters ranging from 12.5 to 50mm and are offered uncoated or with anti-reflective coating.

## Technical Information

