

TECHSPEC® 30mm Dia. x 50mm FL, MgF₂ Coated, Inked, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#32-496-INK** 17 TO 22 D= DAYS

[Other Coating Options](#)

- 1 +

₹11,745.00

ADD TO CART

Qty 1-5

₹11,745.00

Qty 6+

₹9,396.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):

50.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 42.57
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 29.00
Centering (arcmin): <1
Center Thickness CT (mm): 13.20 ±0.20
Center Thickness CT 1 (mm): 11.00 ±0.10
Center Thickness CT 2 (mm): 2.20 ±0.10
Radius R ₁ (mm): 34.81
Radius R ₂ (mm): -22.12
Radius R ₃ (mm): -203.48
Edge Thickness ET (mm): 9.25
Substrate: ☐ N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 1.67
Numerical Aperture NA: 0.30
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View