

30mm Dia. x 100mm FL, 1064nm AR Coated, Gradium Lens

See More by [Lightpath®](#)



Stock #48-444 CLEARANCE 20+ In Stock

-

1

+

₹17,396

ADD TO CART

Volume Pricing	
Qty 1+	₹17,396 each
Need More?	Request Quote

Product Downloads

General

Gradient Index Lens

Type:

Physical & Mechanical Properties

30.00 ±0.25

Diameter (mm):

1.00

Centering (arcmin):

27.00

Clear Aperture CA (mm):

6.00 ±0.1	Center Thickness CT (mm):
Protective as needed	Bevel:
Optical Properties	
100.00 @ 546nm	Effective Focal Length EFL (mm):
0.14	Numerical Aperture NA:
96.53	Back Focal Length BFL (mm):
±1	Focal Length Tolerance (%):
Laser V-Coat (1064nm)	Coating:
R _{avg} <0.25% @ 1064nm	Coating Specification:
40-20	Surface Quality:
3.7	f/#:
Infinite	Conjugate Distance:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Aspheric Performance
- Smaller Focused Spot Size
- Reduced Spherical Aberration

GRADIUM® lenses utilize advances in the manufacturing of axial gradient glass to improve lens performance. The process turns a glass of several SF layers into a single glass with a gradually changing index. The index may change by as much as 0.15 from the front surface to the back surface. This change in index allows for correction of system aberrations, especially spherical, yielding better images in infinite/finite imaging applications. GRADIUM® lenses are ideal for laser focusing applications, providing smaller spot sizes compared to the standard PCX counterpart. Two broadband antireflection coating options are available that cover a large range of visible and near-infrared laser wavelengths. For OEM and high volume coating options, please contact our [Applications Engineering Department](#) to discuss your requirements.

Technical Information



