

[See all 70 Products in Family](#)

## TECHSPEC® 30mm Diameter, 785nm V-Coat, $\lambda/4$ N-BK7 Window

See More by [SCHOTT Optical Components](#)



Stock #64-052 **20+ In Stock**

- 1 + MRP ₹12,107

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹12,107 each
Qty 6-25	₹9,685 each
Qty 26-49	₹9,131 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Laser Line Window **Type:**

Glass **Type of Window:**

### Physical & Mechanical Properties

**Clear Aperture CA (mm):**

27.00

30.00 +0.00/-0.25

Diameter (mm):

4.00 ±0.20

Thickness (mm):

≤1

Parallelism (arcmin):

Protective as needed

Bevel:

90

Clear Aperture (%):

Fine Ground

Edges:

0.21

Poisson's Ratio:

82

Young's Modulus (GPa):

610.00

Knoop Hardness (kg/mm<sup>2</sup>):

## Optical Properties

Laser V-Coat (785nm)

Coating:

785

Design Wavelength DWL (nm):

**N-BK7**

Substrate:

1.516

Index of Refraction (n<sub>d</sub>):

60-40

Surface Quality:

64.17

Abbe Number (v<sub>d</sub>):

R<sub>abs</sub> <0.25% @ 785nm

Coating Specification:

λ/4

Surface Flatness (P-V):

## Material Properties

2.51

Density (g/cm<sup>3</sup>):

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):  
7.1 (-30 to +70°C)  
8.3 (+20 to +300°C)

## Regulatory Compliance

**Compliant**

RoHS 2015:

[View](#)

Certificate of Conformance:

**Compliant**

Reach 235:

United States

Country of Origin:

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- <0.25% Reflection at Design Wavelength
- Coatings Available for HeNe, Diode, and Nd:YAG Laser Sources
- Precision N-BK7 Substrate
- Also Available [Uncoated](#), [MgF<sub>2</sub> Coated](#) and [VIS 0° Coated](#)

TECHSPEC® N4 N-BK7 Laser Line Windows are ideally suited for industrial and low power laser applications. The high tolerance design yields minimal beam distortion and scatter. Anti-reflection coatings provide <0.25% reflection at the coating's design wavelengths.



## Technical Information



## Compatible Mounts