

TECHSPEC® 30mm Dia. x 50mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-371-INK** 17 TO 22 D= DAYS
[Other Coating Options](#)

- 1 + **₹13,398.00**

ADD TO CART

Qty 1-5
₹13,398.00
Qty 6+
₹10,723.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):
50.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 42.57
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 29.00
Centering (arcmin): <1
Center Thickness CT (mm): 13.20 ±0.20
Center Thickness CT 1 (mm): 11.00 ±0.10
Center Thickness CT 2 (mm): 2.20 ±0.10
Radius R₁ (mm): 34.81
Radius R₂ (mm): -22.12
Radius R₃ (mm): -203.48
Edge Thickness ET (mm): 9.25
Substrate: ☐ N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 1.67
Numerical Aperture NA: 0.30
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View