

# 30x60mm Half Mirror Coaxial Light Blue

See More by [CCS](#)



Stock **#21-834** CLEARANCE **1 In Stock**

-

1

+

₹1,49,027

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹1,49,027 each                |
| Need More?     | <a href="#">Request Quote</a> |

|                   |
|-------------------|
| Product Downloads |
|-------------------|

## SPECIFICATIONS

| General         |                       |
|-----------------|-----------------------|
| LFV3-G-30X60BL  | Model Number:         |
| LED Illuminator | Type of Illumination: |
| CCS             | Manufacturer:         |

|                                                                                                                                                                                                                                      |                             |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| Coaxial Light                                                                                                                                                                                                                        | Geometry:                   |
| Constant                                                                                                                                                                                                                             | Illumination Mode:          |
| Physical & Mechanical Properties                                                                                                                                                                                                     |                             |
| W68 mm xD 60 mm xH 35 mm                                                                                                                                                                                                             | Dimensions (mm):            |
| 165                                                                                                                                                                                                                                  | Weight (g):                 |
| 30 mm x60 mm                                                                                                                                                                                                                         | Active Area (mm):           |
| Optical Properties                                                                                                                                                                                                                   |                             |
| Blue                                                                                                                                                                                                                                 | Color:                      |
| 470                                                                                                                                                                                                                                  | Wavelength (nm):            |
| Electrical                                                                                                                                                                                                                           |                             |
| 8                                                                                                                                                                                                                                    | Power Consumption (W):      |
| Hardware & Interface Connectivity                                                                                                                                                                                                    |                             |
| 24                                                                                                                                                                                                                                   | Input Voltage (V):          |
| Power Supply:<br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#73-491</a><br>Europe: <a href="#">#73-491</a><br>Japan: <a href="#">#89-513</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#73-491</a> |                             |
| Regulatory Compliance                                                                                                                                                                                                                |                             |
| <a href="#">Exempt</a>                                                                                                                                                                                                               | RoHS 2015:                  |
| <a href="#">Contains SVHC(s)</a>                                                                                                                                                                                                     | Reach 224:                  |
| <a href="#">View</a>                                                                                                                                                                                                                 | Certificate of Conformance: |

## PRODUCT DETAILS

- Unique Design Prevents Ghost Images
- Available in Red, White, and Blue
- Ideal for Use with High Resolution Cameras

CCS High-Resolution Coaxial Lights are designed to provide diffused lighting for high-resolution imaging of shiny, flat surfaces. Designed to prevent ghost reflections and achieve higher system resolution, these coaxial lights integrate a unique thin beamsplitter to minimize deviation through in the imaging path. CCS High-Resolution Coaxial Lights are ideal for industrial imaging applications including inspection of glossy surfaces, pattern detection on PCBs, and measuring dimensions of glass.

## TECHNICAL INFORMATION

