

[See all 12 Products in Family](#)

355nm, 1X - 8X Jenoptik Silverline™ Variable Beam Expander

See More by [Jenoptik](#)



Stock **#73-101** [CONTACT US](#)

-

1

+

₹2,29,050

ADD TO CART

Volume Pricing	
Qty 1-4	₹2,29,050 each
Qty 5+	₹2,06,100 each
Need More?	Request Quote

Product Downloads

General	
Beam Expander	Type:
Variable Magnification	Style:
Physical & Mechanical Properties	
210.00	Length (mm):
	Weight (g):

540	
	Housing Diameter (mm):
55.0	
	Pointing Accuracy (mrad):
<0.3	
Optical Properties	
	Entrance Aperture (mm):
9.0 - 4.0 (1X - 8X)	
	Expansion Power:
1X - 8X	
	Substrate: ☐
Entrance: Fused Silica Exit: Fused Silica	
	Transmission (%):
≥97	
	Design Wavelength DWL (nm):
355	
	Damage Threshold, Reference: ☐
CW: 0.10 MW/cm² Pulsed (ns): 0.10 J/cm²	
	GDD Specification (fs²):
2810	
Threading & Mounting	
	Mounting Threads:
Input: M30 X 1.0 Output: SM2	
Regulatory Compliance	
	Certificate of Conformance:
View	
	Country of Origin:
Lithuania	
	Imported By:
Edmund Optics India Private Limited	

Product Details

- Ideal for High-Power and Ultrashort Pulse Systems
- Continuous Magnifications Ranges from 1X to 10X
- Designed for Diffraction Limited Performance

Jenoptik Variable Magnification Beam Expanders provide excellent performance with high damage thresholds for the demanding requirements of laser materials processing. These beam expanders are coated to maximize transmission at common Nd:YAG and Fiber Laser Wavelengths, and are available in a variety of design forms and zoom ranges. The standard variable magnification beam expanders are available in a 1X to 4X or 2X to 10X configuration and features all fused silica optics, and designs for either 355nm, 515-540nm, or 1030-1080nm. The 1X to 4X steadfast versions are available in the same wavelength ranges and feature a mechanical design that guides the movable optical elements in a stable, linear manner to reduce the influences of vibrations or system accelerations. The Silverline™ series are designed for high performance and ensure diffraction-limited image quality over the entire 1X to 8X magnification range. Jenoptik Variable Magnification Beam Expanders are ideal for a range of high-power laser material processing applications including cutting, welding, and engraving for metals, polymers, or ceramics.