

[See all 22 Products in Family](#)

35mm Dia. x 35mm FL Protected Aluminum, Concave Mirror



Stock #43-468 **1 In Stock**

- 1 + MRP ₹5,852

i Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-49 | ₹5,852 each |
| Qty 50-99 | ₹4,944 each |
| Need More? | Request Quote |

Product Downloads

General

Spherical Mirror **Type:**

Physical & Mechanical Properties

±0.5 **Thickness Tolerance (mm):**

35.00 ±0.50 **Diameter (mm):**

Clear Aperture (%):

90

Edge Thickness ET (mm):

6.0

Optical Properties

Coating Type:

Metal

Coating:

Protected Aluminum (400-2000nm)

Wavelength Range (nm):

400 - 2000

Effective Focal Length EFL (mm):

35.00

Substrate: □

N-BK7

Aperture (f/#):

f/1

Coating Specification:

R_{avg} >85% @ 400 - 700nm
R_{avg} >90% @ 400 - 2000nm

Focal Length Tolerance (%):

±2

Radius R₁ (mm):

70.00

Surface Quality:

80-50

Radius of Curvature (mm):

70.00

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Ideal for Focusing Light
- Aluminum and Gold Coating Options
- Available in Sizes Ranging from 9 - 50mm

Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

Technical Information



