

## 35mm Diameter x 26.2mm FL, Aspheric Condenser Lens



Stock **#43-988** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹6,760

● Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹6,760 each                   |
| Qty 11-49      | ₹5,953 each                   |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

#### General

Condenser Lens **Type:**

#### Physical & Mechanical Properties

35.00 +0.0/-0.4 **Diameter (mm):**

≤25 **Centering (arcmin):**

|                      |                                  |
|----------------------|----------------------------------|
| 29.1                 | <b>Clear Aperture CA (mm):</b>   |
| 4.0 ±0.30            | <b>Edge Thickness ET (mm):</b>   |
| 13.90 ±0.25          | <b>Center Thickness CT (mm):</b> |
| Protective as needed | <b>Bevel:</b>                    |
| 31.1                 | <b>Diameter of Asphere (mm):</b> |
| Plano                | <b>Shape of Back Surface:</b>    |

## Optical Properties

|                      |   |
|----------------------|---|
| 26.20                | <b>Effective Focal Length EFL (mm):</b>     |
| 0.61                 | <b>Numerical Aperture NA:</b>               |
| 16.30                | <b>Back Focal Length BFL (mm):</b>          |
| <a href="#">B270</a> | <b>Substrate:</b> <input type="checkbox"/>  |
| ±7                   | <b>Focal Length Tolerance (%):</b>          |
| Uncoated             | <b>Coating:</b>                             |
| 80-50 (typical)      | <b>Surface Quality:</b>                     |
| 0.8                  | <b>f#:</b>                                  |
| 58.5                 | <b>Abbe Number (v<sub>d</sub>):</b>         |
| 1.523                | <b>Index of Refraction (n<sub>d</sub>):</b> |
| Plano                | <b>Radius R<sub>2</sub> (mm):</b>           |
| 350 - 2500           | <b>Wavelength Range (nm):</b>               |
| Infinite             | <b>Conjugate Distance:</b>                  |

## Material Properties

|     |   |
|-----|---|
| 9.4 | <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b> |
|-----|---|

## Regulatory Compliance

|   |                                    |
|---|------------------------------------|
| <a href="#">Compliant</a>   | <b>RoHS 2015:</b>                  |
| <a href="#">Compliant</a>   | <b>Reach 224:</b>                  |
| <a href="#">View</a>  | <b>Certificate of Conformance:</b> |
| Germany   | <b>Country of Origin:</b>          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | <b>Imported By:</b>                |

## Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

## Technical Information

