


3.3mm² Two-Element Segmented Photodiode



Stock **#84-609** **3 In Stock**

- 1 + ₹3,915

ADD TO CART

Volume Pricing

Qty 1-4	₹3,915 each
Qty 5-9	₹3,465 each
Qty 10+	₹3,083 each
Need More?	Request Quote

Product Downloads

General

22.00 **Rise Time (ns):**

SPOT-2D **Model Number:**

Physical & Mechanical Properties

1.3x2.5 **Size of Active Area (mm):**

3.3 **Active Area (mm²):**

0.127 **Element Gap (mm):**

Electrical

Responsivity @ 970nm (AW):
Minimum: 0.6
Typical: 0.65

Capacitance @ V_R=-10V (pF):
11.00

Noise Equivalent Power NEP (W/ Hz^{1/2}):
1.1 x 10⁻¹⁴ @ -10 V, 970nm

Maximum Reverse Voltage (V):
30.00

Dark Current @ V_R=-10V (nA):
Maximum: 2
Typical: 0.15

Hardware & Interface Connectivity

Connector:
41 / TO-5

Environmental & Durability Factors

Operating Temperature (°C):
-40 to 100

Storage Temperature (°C):
-55 to 125

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
Philippines

Imported By:
Edmund Optics India Private Limited

Product Details

- High Stability Over Temperature and Time
- Excellent Resolution, High Accuracy, Ultra-Low Dark Current
- Two or Four Separate Active Area Segments
- [Segmented InGaAs Photodiodes](#) Also Available

Segmented Photodiodes are designed for a wide variety of applications that require high stability and fast response times. Featuring position resolutions of greater than 0.1µm, Segmented Photodiodes are ideal for surface profiling, position measurement, alignment, or targeting. Segmented Photodiodes are segmented into either two or four separate active areas and have spectral response ranges from 350 – 1100nm. The segmented regions allow various measurement profiles on a single detector.