

[See all 17 Products in Family](#)

**TECHSPEC® 320 - 370nm, 25.4mm Dia., Ultrafast Mirror**



Stock #12-464 [CONTACT US](#)

- 1 + ₹18,295

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹18,295 each
Qty 6-9	₹16,193 each
Qty 10+	₹14,402 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror **Type:**  
  
 Typical Applications:  
 Yb:doped Lasers 3rd Harmonic

**Physical & Mechanical Properties**

Clear Aperture (%):  
 >80

Commercial Polish	<b>Back Surface:</b>
25.40 +0.00/-0.10	<b>Diameter (mm):</b>
6.35 ±0.10	<b>Thickness (mm):</b>
<10	<b>Parallelism (arcsec):</b>
<5	<b>Surface Roughness (□):</b>

## Optical Properties

10-5	<b>Surface Quality:</b>
98.5	<b>Reflection at DWL (%):</b>
R <sub>s</sub> >99.75% @ 320 - 370nm R <sub>p</sub> >99.5% @ 327 - 363nm	<b>Coating Specification:</b>
0 ±10fs <sup>2</sup> @ 320 - 370nm (s-pol), @ 330 - 360nm (p-pol)	<b>GDD Specification:</b>
320 - 370	<b>Wavelength Range (nm):</b>
λ/10	<b>Surface Flatness (P-V):</b>
Dielectric	<b>Coating Type:</b>
Ultrafast (320-370nm)	<b>Coating:</b>
343	<b>Design Wavelength DWL (nm):</b>
45	<b>Angle of Incidence (°):</b>

<b>Fused Silica</b> (Corning 7980)	<b>Substrate:</b> □
0.55 J/cm <sup>2</sup> @ 343nm, 180fs FWHM, S-polarization, 1 pulse (typical) 0.25 J/cm <sup>2</sup> @ 343nm, 180fs FWHM, S-polarization, 1000 pulses (typical) 0.37 J/cm <sup>2</sup> @ 343nm, 180fs FWHM, P-polarization, 1 pulse (typical) 0.22 J/cm <sup>2</sup> @ 343nm, 180fs FWHM, P-polarization, 1000 pulses (typical) 0.35 J/cm <sup>2</sup> @ 343 nm, 1 ps FWHM, 100 Hz P-polarization, 1000 pulses	<b>Damage Threshold, By Design:</b> □

## Regulatory Compliance

<b>Compliant</b>	<b>RoHS 2015:</b>
<b>Compliant</b>	<b>Reach 205:</b>
<b>View</b>	<b>Certificate of Conformance:</b>


## Product Details

- Designed with High Reflectivity for Ultrafast Beam Steering
- Ion-Beam Sputtered Coating for Low Scatter and Absorption
- GDD as Low as 0±20fs<sup>2</sup> at Design Wavelength Range

TECHSPEC® High Performance Low GDD Ultrafast Mirrors are designed to have high reflectivity at 0° or 45° angles of incidence, making them ideal for ultrafast laser beam steering applications. These mirrors have a dispersion compensating coating obtained through a precision ion beam sputtering (IBS) process, providing lower scatter and absorption than traditional dielectric laser mirrors. TECHSPEC High Performance Low GDD Ultrafast Mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. Typical applications include use in the transport of femtosecond laser pulses.

**Note:** Please [contact us](#) if your application requires a TECHSPEC High Performance Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---