

[See all 6 Products in Family](#)

3.45X 65mm WD, In-Line Illumination 1.2" Telecentric Lens



1.2" Sensor In-Line Illumination Telecentric Lenses

Stock **#72-175** **1 In Stock**

-

1

+

MRP ₹4,30,110

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹4,30,110 each
Need More?	Request Quote

Product Downloads

General	
Product Family: 1.2" Sensor In-Line Illumination Telecentric Lenses	
Type: Telecentric Lens	
Compatible Light Guide/Source: 1/4" (0.312")	
Type of Illumination: In-Line Illumination	
Physical & Mechanical Properties	

160.00	Length (mm):
0.312	Ferrule Diameter (inches):
19.3	Maximum Diameter (mm):

Optical Properties	
4.20mm	Horizontal Field of View @ Max Sensor Format:
2.3mm	Horizontal Field of View, 2/3" Sensor:
3.4mm	Horizontal Field of View, 1/2" Sensor:
19.30	Maximum Image Circle (mm):
3.45X	Primary Magnification PMAG:
3.45	Telecentric Lens Magnification:
65.00	Working Distance (mm):
f/10.1	Aperture (f/#):
<0.01%	Distortion (%):
3.45X	Magnification:
VS	Lens Wavelength Range:

Sensor	
1.2"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting	
N/A	Filter Thread:
C-Mount	Mount:

Regulatory Compliance	
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- 1.2" Max Sensor Format
- Fiber Optic Input for In-line Illumination
- Long Working Distance

1.2" Sensor In-Line Illumination Telecentric Lenses are designed for cameras with SONY IMX367, 530, and 540 or equivalents allowing for large fields of view. Theses lenses are designed with an in-line illumination port that accepts a 1/4" fiber optic light guide with incorporated M3 set screws in the in-line illumination port to light guide and include a lockable ring to rotate the lens and ensure alignment with the camera sensor. These telecentric lenses are designed to achieve high coaxial uniformity on 3µm, 24.5MP sensors and reduce parallax errors yielding maximum image quality with an excellent degree of measurement accuracy. 1.2" Sensor In-Line Illumination Telecentric Lenses are available in magnifications ranging from 0.5X– 3.45X and offer low f/#s and a low distortion of <0.01%. These lenses are ideal for applications including machine vision, metrology, automotive and electronic inspection, measurement, and gauging.

Note: 1/4" [Fiber optic light guides](#) are sold separately.