


34mm² DUV Photodiode with Ceramic Housing



DUV Photodiodes

Stock #84-985 **2 In Stock**

1 MRP ₹13,594

Price inclusive of all taxes

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | ₹13,594 each |
| Qty 5-9 | ₹12,107 each |
| Qty 10-24 | ₹10,779 each |
| Need More? | Request Quote |

Product Downloads

General

1 @ 0 V, 1 kΩ **Rise Time (μs):**

Physical & Mechanical Properties

5.8 x 5.8 **Size of Active Area (mm):**

Active Area (mm²):

Optical Properties

980.00 **Peak Response Wavelength (nm):**

Electrical

0.5 **Responsivity @ 980nm (AW):**

Minimum: 0.1
Typical: 0.4 **Shunt Resistance @ V=-10mV (GΩ):**

0.34 **Responsivity @ 633nm (AW):**

0.12 **Responsivity @ 200nm (AW):**

380.00 **Capacitance @ V_R=0V (pF):**

5.8×10^{-14} **Noise Equivalent Power NEP (W/ Hz^{1/2}):**
@ 0 V, 200nm

5.00 **Maximum Reverse Voltage (V):**

Hardware & Interface Connectivity

Ceramic **Connector:**

Environmental & Durability Factors

-20 to +60 **Operating Temperature (°C):**

-20 to +80 **Storage Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Malaysia **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Excellent UV Sensitivity
- High Shunt Resistance
- Low Capacitance

DUV Photodiodes are ideal for a wide variety of applications, including UV spectrophotometry and analytical and medical instrumentation. DUV Photodiodes are designed for enhanced responsivity from 200 – 400nm, and with sensitivity extending down to 190nm. DUV Photodiodes feature quartz windows and either metal or ceramic housing. Models with suppressed NIR performance are also available.