

TECHSPEC[®] 35mm FL f/2.5, Blue Series M12 Lens



Stock **#70-644** [CONTACT US](#)

-

1

+

MRP ₹13,275

Price inclusive of all taxes


ADD TO CART

Volume Pricing	
Qty 1-49	₹13,275 each
Qty 50+	₹10,408 each
Need More?	Request Quote

Product Downloads

General	
Blue Series	Product Family:
Required Accessories: #63-956 and #64-102	Note:
M12 Imaging Lens	Type:

No	IR Cut Filter:
High Performance M12 Lens	Imaging Lens Type:
Physical & Mechanical Properties	
Fixed	Iris Option:
29.50	Length (mm):
18.0	Maximum Diameter (mm):
18	Outer Diameter (mm):
Optical Properties	
11.6°	Horizontal Field of View @ Max Sensor Format:
11.6°	Horizontal Field of View, 1/1.8" Sensor:
10.4°	Horizontal Field of View, 1/2" Sensor:
9.4°	Horizontal Field of View, 1/2.5" Sensor:
7.8°	Horizontal Field of View, 1/3" Sensor:
5.8°	Horizontal Field of View, 1/4" Sensor:
9.00	Maximum Image Circle (mm):
0.024	Numerical Aperture NA, Object Side:
6(5)	Number of Elements (Groups):
400 - 700	Wavelength Range (nm):
35.00	Focal Length FL (mm):
150 - ∞	Working Distance (mm):
f/2.5	Aperture (f/#):
0.08 @ Full Field	Distortion (%):
18.72-8.41	Back Focal Length BFL (mm):
λ/4 MgF ₂ @ 550nm	Coating Specification:
38.88439	Entrance Pupil Position (mm):
3.13	Object Space Principal Plane (mm):
-40.60	Image Space Principal Plane (mm):
-0.08	Maximum Distortion (%):
-22.91602	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:
Sensor	
1/1.8"	Maximum Sensor Format:
1.40	Pixel Size (μm):
Threading & Mounting	
N/A	Filter Thread:
S-Mount (M12 x0.5)	Mount:
Regulatory Compliance	



*Specified for Optimized Working Distance of 150 - 250mm.

;