

[See all 30 Products in Family](#)

**TECHSPEC® 35.0mm 750 - 1100nm, N-BK7 Right Angle Mirrors (Hypotenuse Coated)**



Broadband Dielectric Coated Right Angle Mirrors

Stock **#87-403** **2 In Stock**

⊖ 1 ⊕ MRP ₹30,974

📌 Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹30,974 each
Qty 6-25	₹24,719 each
Qty 26-49	₹23,205 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Right Angle Mirror **Type:**

**Physical & Mechanical Properties**

90 **Clear Aperture (%):**

**Dimensional Tolerance (mm):**

±0.1

Length of Hypotenuse (mm):

49.50

Length of Legs (mm):

35.00

## Optical Properties

Coating Type:

Dielectric

Coating:

Dielectric Mirror (750-1100nm)

Wavelength Range (nm):

750 - 1100

Substrate:

N-BK7

Angle Tolerance (arcmin):

±2

Coating Specification:

Hypotenuse:  $R_{avg} > 98\%$  @ 750 - 1100nm (0 - 45°)

$R_{avg} > 99\%$  @ 750 - 1100nm (0°)

Surface Quality:

40-20

Damage Threshold, By Design:

1 J/cm<sup>2</sup> @ 1064nm, 20ns, 20Hz

Power (fringes) @ 632.8nm:

1.25

Irregularity (fringes) @ 632.8nm:

0.50

## Regulatory Compliance

RoHS 2015:

Compliant

Reach 209:

Compliant

Certificate of Conformance:

[View](#)

Country of Origin:

Singapore

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Greater Than 98% Reflection Over Broad Wavelength Ranges
- High Reflectivity for all Polarization States
- Reflect Light at 90°
- [Standard Metal Coated Right Angle Mirrors](#) Also Available

TECHSPEC® Broadband Dielectric Coated Right Angle Mirrors (Hypotenuse Coated) are designed for beam steering or precision alignment applications utilizing multiple laser sources or operating from the visible to near-infrared spectra. These mirrors feature improved reflection compared to standard metal coated mirrors, increasing system performance by decreasing energy loss. These right angle mirrors are easily mounted and integrated into optical systems. TECHSPEC® Broadband Dielectric Coated Right Angle Mirrors (Hypotenuse Coated) reflect light at 90° and have greater than 98% reflection over broad wavelength ranges. These mirrors feature a N-BK7 substrate and are available in a variety of leg lengths.

**Note:** These right angle mirrors are not recommended for use in applications where light is reflected off the coated hypotenuse from inside the prism.

## Technical Information




Image above shows light reflecting off the coated hypotenuse.

---

;