


[See all 2 Products in Family](#)

Siemens Star Target Array, 50 x 50mm, 33 Stars, 36 Sectors Chrome on Glass



Stock #58-834 **3 In Stock**

- 1 + MRP ₹47,684

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹47,684 each
Qty 5+	₹45,401 each
Need More?	Request Quote

Product Downloads

General

No NIST Certification:

Physical & Mechanical Properties

2.00 Individual Star Diameter (mm):

36.00 Number of Sectors:

Number of Stars:

33.00

29.20 x 21.00

Pattern Size (mm):

50 x 50 ±0.1

Dimensions (mm):

1.50 ±0.05

Thickness (mm):

Optical Properties

High Reflective Chrome

Coating:

2.86 - 57.5

Frequency (lp/mm):

Float Glass

Substrate: □

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[Compliant](#)

Reach 223:

[View](#)

Certificate of Conformance:

Switzerland

Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Detect Aberrations at Various Field Points

Our star target arrays are designed to identify focus errors and astigmatism along field points in the image of a vision system. With star targets located at the center, corner, and along the diagonals of the sensor, determining precision location and amplitude of the problem areas couldn't be easier. The small array features unresolved centers of 0.1mm, whereas the large array features unresolved centers of 0.15mm.

;