

[See all 8 Products in Family](#)

355nm Solid State Laser



355nm Solid State Laser & Included Power Supply, #39-182



Stock **#39-182** 1 In Stock

-

1

+

₹10,98,000

ADD TO CART

Volume Pricing	
Qty 1+	₹10,98,000 each
Need More?	Request Quote

Product Downloads



General	
<10	Warm-Up Time (minutes):
IIIb	Laser Class - CDRH:
5000	Mean Time to Failure MTTF (hours):
Physical & Mechanical Properties	

321.0 x 99.0 x 94.0	Dimensions (mm):
70	Beam Height from Base Plate (mm):
Optical Properties	
25:1	Polarization:
355.00	Wavelength (nm):
<1.2	Mode Quality, M ² :
±1	Wavelength Tolerance (nm):
1.0	Beam Diameter (mm):
<1.5	Beam Divergence (mrad):
UV	Color:
<2	Pulse Duration (ns):
2.45	Single Pulse Energy (μJ):
Electrical	
<2% RMS over 4 hours	Power Stability (%):
22	Average Output Power (mW):
9	Repetition Rate (kHz):
Hardware & Interface Connectivity	
Power Supply Included. Dimensions: 307.0 x 150.0 x 106.0mm	Power Supply:
100-240VAC	Power Requirement:
Free Space	Output Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

Product Details

- Class IIIb High Power Lasers
- 10mW Average Power
- <2ns Pulse Duration
- 355nm Frequency Converted Q-Switched

355nm Solid State Lasers are diode-pumped and generate UV light by frequency conversion of Q-Switched pulses. These lasers feature pulse durations less than 2ns and an average output power of 10mW. 355nm Solid State Lasers feature a compact form factor and are used for high power UV applications including UV curing, laser medical treatments, and micro-electronics manufacturing. An integrated thermoelectric cooler (TEC) promotes a long expected lifetime of 5000 hours.

Note: Power supply included.