

**TECHSPEC® 35mm Dia Protected Gold, 4-6λ Mirror**



Stock **#46-028** [CONTACT US](#)

⊖ 1 ⊕ MRP ₹8,071

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹8,071 each
Qty 6-25	₹6,255 each
Qty 26-99	₹5,650 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Flat Mirror **Type:**

**Physical & Mechanical Properties**

35.00 ±0.25 **Diameter (mm):**

3.00 nominal **Thickness (mm):**

33.25 Clear Aperture CA (mm):

±0.25 Dimensional Tolerance (mm):

Edges:  
Ground, 0.5mm Maximum Edge Chip

## Optical Properties

Metal Coating Type:

Protected Gold (700-10000nm) Coating:

4 - 6λ Surface Flatness (P-V):

700 - 10000 Wavelength Range (nm):

Float Glass Substrate: □

Coating Specification:  
R<sub>avg</sub> >96% @ 700 - 2000nm  
R<sub>avg</sub> >96% @ 2000 - 10,000nm

60-40 Surface Quality:

0.8 J/cm<sup>2</sup> @ 1064nm, 10ns Damage Threshold, Reference: □

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

United States Country of Origin:

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Wide Variety of Shapes and Sizes Available
- Enhanced Aluminum, Protected Gold, and Protected Silver Coatings for high reflectivity from 450-10000nm
- [Contact Us](#) for Custom Sizes

TECHSPEC® First Surface Mirrors feature a high reflectivity coating deposited on the front surface of the glass substrate. The mirrors are available in enhanced aluminum, protected gold, and protected silver coatings for high reflectivity from 450-10000nm. The coated surface should be oriented to reflect incident light. TECHSPEC First Surface Mirrors are offered in circular, square, and rectangular dimensions. First surface mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. These first surface mirrors easily mount into a [range of optical mounts](#) to facilitate application integration.

Note: A range of mounts specifically compatible with individual TECHSPEC® First Surface Mirrors can be found on product web pages.

TECHSPEC® First Surface Mirrors feature a high-reflectivity coating deposited on the front surface of a float-glass substrate to minimize ghosting and enable accurate beam redirection.

They are available with enhanced aluminum, protected silver, and protected gold coatings for applications requiring high reflectivity from 450 – 10000nm.


These mirrors are ideal for optical path folding, beam steering, and imaging systems where the mirror is mounted at 45° to produce a 90° bend in the light path.

Offered in circular, square, and rectangular formats, they are well-suited for OEM integration, prototype builds, and general laboratory alignment setups. With typical surface flatness of 4 – 6λ (waves) and 60-40 surface quality, they provide a cost-effective solution for applications that require reliable reflected beam performance without the added expense of precision polished substrates.

First-surface mirrors are commonly used in life sciences, metrology, semiconductor, and general photonics systems where the quality of reflected light is important.

For proper use, the coated surface should be oriented toward the incident light to avoid transmission through the substrate and preserve optical performance.

## Technical Information



## Compatible Mounts

---