

TECHSPEC® 35mm Focal Length, UAV Series Fixed Focal Length Lens



TECHSPEC® UAV Series Fixed Focal Length Lenses



Stock **#22-838** [CONTACT US](#)

-

1

+

₹70,079

ADD TO CART

Volume Pricing	
Qty 1+	₹70,079 each
Need More?	Request Quote

Product Downloads

General	
UAV Series	Series:
Fixed Focal Length Lens	Type:
Infinite Conjugate	Imaging Lens Type:
Physical & Mechanical Properties	
Variable	Iris Option:

62.76	Length (mm):
38.8	Outer Diameter (mm):
110	Weight (g):
4.0	Maximum Rear Protrusion (mm):
62.76	Maximum Length (mm):

Optical Properties

23.7°	Horizontal Field of View @ Max Sensor Format:
23.7°	Horizontal Field of View, 1.2" Sensor:
28.4°	Horizontal Field of View, 1.1" Sensor:
25.9°	Horizontal Field of View, 1" Sensor:
17.9°	Horizontal Field of View, 2/3" Sensor:
14.7°	Horizontal Field of View, 1/1.8" Sensor:
19.30	Maximum Image Circle (mm):
0.00124	Numerical Aperture NA, Object Side:
8 (6)	Number of Elements (Groups):
425 - 675	Wavelength Range (nm):
35.00	Focal Length FL (mm):
500 - ∞	Working Distance (mm):
FOV @ Max Sensor Format, H x V (mm): Horizontal: 23.7° Vertical: 20.5° Diagonal: 31.1°	
f/2.8 - f/16	Aperture (f/#):
425 - 675 BBAR	Coating:
425 - 675 BBAR	Coating Specification:

34.468	Entrance Pupil Position (mm):
-36.97	Object Space Principal Plane (mm):
-36.73	Image Space Principal Plane (mm):
1	Maximum Distortion (%):
-34.396	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

Sensor

1.2"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

M37.0 x0.75 (Male)	Filter Thread:
M37.0 x0.75	Front Thread:
C-Mount	Mount:

Environmental & Durability Factors

-20 to +60 For questions regarding operating temperature please contact our support team	Storage Temperature (°C):
--	---------------------------

Regulatory Compliance

View		Certificate of Conformance:
China		Country of Origin:
Edmund Optics India Private Limited		Imported By:


Product Details

- Compact, Infinite Conjugate Lens Ideal for Photogrammetry
- 8mm, 12mm, 16mm, 25mm, and 35mm Focal Lengths
- 1.2", C-Mount Lens
- Up to 24.4 MegaPixels, 2.7µm Pixel Size Sensors


TECHSPEC® UAV Series Fixed Focal Length Lenses are compact, lightweight infinite conjugate lenses designed for the 4th Generation Sony Pregius 1.2" IMX530 and IMX540 sensors for mounting on autonomous vehicles and drones. These lenses are designed with a low Ground Separation Distance (GSD) to enable accurate survey results, and are available in 8mm, 12mm, 16mm, 25mm, and 35mm focal length options. The f/2.8 aperture provide increased light throughput and high-resolution performance. TECHSPEC® UAV Series Fixed Focal Length Lenses are C-Mount and feature a locking focus and iris rings to prevent unwanted adjustments, as well as a front filter thread for integrating standard [optical filters](#). These lenses are ideal for Drone Mapping and Surveying, Aerial Imaging, and Photogrammetry applications.

Note: Call for OEM Quantity and Pricing


Technical Information




#22-838 - 35mm Focal Length, UAV Series Fixed Focal Length Lens, Distortion Plot



#22-838 - 35mm Focal Length, UAV Series Fixed Focal Length Lens, Relative Illumination Plot



#22-838 - 35mm Focal Length, UAV Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, Infinity Working Distance, f2.8



#22-838 - 35mm Focal Length, UAV Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, Infinity Working Distance, f4

