

[See all 10 Products in Family](#)

38.1mm Dia., Gold Coated, Aluminum Substrate Mirror



Metal Substrate Mirrors

Stock **#47-116** **6 In Stock**

-

1

+

₹28,493

ADD TO CART

Volume Pricing	
Qty 1-5	₹28,493 each
Qty 6-25	₹25,613 each
Qty 26-49	₹24,211 each
Need More?	Request Quote

Product Downloads

General	
Flat Mirror	Type:
Physical & Mechanical Properties	
38.10 +0.00/-0.38	Diameter (mm):
9.50	Thickness (mm):

90	Clear Aperture (%):
<175	Surface Roughness (□):
Optical Properties	
0.7 - 12	Wavelength Range (μm):
Metal	Coating Type:
Protected Gold (700-12000nm)	Coating:
700 - 12000	Wavelength Range (nm):
Aluminum 6061-T6	Substrate: □
Ravg >94% @ 700 - 800nm Ravg >97% @ 800 - 2000nm Ravg >98% @ 2 - 12μm	Coating Specification:
80-50	Surface Quality:
λ/4	Surface Flatness (RMS):


Threading & Mounting	
6-32 TPI Tapped Holes	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Aluminum Substrate Mirrors
- Ideal for LWMR Laser Applications
- Aluminum and Gold Coating Options

Metal Substrate Mirrors are available with either a protected aluminum or gold coating and are ideal for LWMR (greater than 2000nm) laser applications. Due to the 17.5nm roughness of the diamond turned surface, these mirrors may not be suitable for UV and visible applications that require low scatter. The backs of the mirrors are machined flat and are tapped with 3 holes for easy, accurate mounting. Metal Substrate Mirrors are aluminum substrate, diamond turned metal mirrors. These mirrors are available in five diameters: 25.4, 38.1, 50.8, 76.2, and 101.6mm.

Technical Information



Compatible Mounts

;