

[See all 413 Products in Family](#)

TECHSPEC[®] 25.4mm Dia. x 35.0mm FL, VIS-EXT Coated, Plano-Convex Lens



Stock **#38-472** **1 In Stock**

☐ [Other Coating Options](#)

-

1

+

₹3,970

ADD TO CART

Volume Pricing	
Qty 1-9	₹3,970 each
Qty 10-24	₹3,562 each
Qty 25-49	₹3,172 each
Need More?	Request Quote

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

25.40 +0.0/-0.025

<1	Centering (arcmin):
6.90 ±0.10	Center Thickness CT (mm):
1.69	Edge Thickness ET (mm):
24.4	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties	
35.00 @ 587.6nm	Effective Focal Length EFL (mm):
30.46	Back Focal Length BFL (mm):
VIS-EXT (350-700nm)	Coating:
R _{avg} <0.5% @ 350 - 700nm	Coating Specification:
N-BK7	Substrate: □
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
18.09	Radius R ₁ (mm):
1.38	f/#:
0.36	Numerical Aperture NA:
350 - 700	Wavelength Range (nm):
5 J/cm² @ 532nm, 10ns	Damage Threshold, By Design: □

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Visible Broadband Anti-Reflection Coating with Extended UV Performance
 - AR Coated to Provide <0.5% Reflectance per Surface for 350 - 700nm
 - Designed for 0° Angle of Incidence
 - Various PCX Coating Options: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), and [YAG-BBAR](#)
- TECHSPEC® VIS-EXT Coated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. TECHSPEC® VIS-EXT Coated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered [uncoated](#) or with broadband anti-reflective (BBAR) coatings, which include [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), and [YAG-BBAR](#).

Technical Information



N-BK7																									
Uncoated N-BK7 Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>400</td><td>92</td></tr><tr><td>600</td><td>92</td></tr><tr><td>800</td><td>92</td></tr><tr><td>1000</td><td>92</td></tr><tr><td>1200</td><td>92</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>92</td></tr><tr><td>1800</td><td>92</td></tr><tr><td>2000</td><td>92</td></tr><tr><td>2200</td><td>92</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	400	92	600	92	800	92	1000	92	1200	92	1400	92	1600	92	1800	92	2000	92	2200	92	Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	70																								
400	92																								
600	92																								
800	92																								
1000	92																								
1200	92																								
1400	92																								
1600	92																								
1800	92																								
2000	92																								
2200	92																								
N-BK7 with MgF₂ Coating Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>98</td></tr><tr><td>1000</td><td>98</td></tr><tr><td>1200</td><td>98</td></tr><tr><td>1400</td><td>98</td></tr><tr><td>1600</td><td>98</td></tr><tr><td>1800</td><td>98</td></tr><tr><td>2000</td><td>98</td></tr><tr><td>2200</td><td>98</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	400	98	600	98	800	98	1000	98	1200	98	1400	98	1600	98	1800	98	2000	98	2200	98	Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	70																								
400	98																								
600	98																								
800	98																								
1000	98																								
1200	98																								
1400	98																								
1600	98																								
1800	98																								
2000	98																								
2200	98																								
N-BK7 with VIS-EXT Coating Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>98</td></tr><tr><td>1000</td><td>98</td></tr><tr><td>1200</td><td>98</td></tr><tr><td>1400</td><td>98</td></tr><tr><td>1600</td><td>98</td></tr><tr><td>1800</td><td>98</td></tr><tr><td>2000</td><td>98</td></tr><tr><td>2200</td><td>98</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	400	98	600	98	800	98	1000	98	1200	98	1400	98	1600	98	1800	98	2000	98	2200	98	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	70																								
400	98																								
600	98																								
800	98																								
1000	98																								
1200	98																								
1400	98																								
1600	98																								
1800	98																								
2000	98																								
2200	98																								
N-BK7 with VIS-NIR Coating Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>98</td></tr><tr><td>1000</td><td>98</td></tr><tr><td>1200</td><td>98</td></tr><tr><td>1400</td><td>98</td></tr><tr><td>1600</td><td>98</td></tr><tr><td>1800</td><td>98</td></tr><tr><td>2000</td><td>98</td></tr><tr><td>2200</td><td>98</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	400	98	600	98	800	98	1000	98	1200	98	1400	98	1600	98	1800	98	2000	98	2200	98	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	70																								
400	98																								
600	98																								
800	98																								
1000	98																								
1200	98																								
1400	98																								
1600	98																								
1800	98																								
2000	98																								
2200	98																								

N-BK7 with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with YAG-BBAR Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 532\text{nm}$ $R_{abs} \leq 0.25\% @ 1064\text{nm}$ $R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\% @ 750 - 800\text{nm}$ $R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}$ $R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness

- Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts

;