

[See all 6 Products in Family](#)

395nm UV LED Pen Kit



Stock #20-617 **14 In Stock**

- 1 + MRP ₹1,34,343

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹1,34,343 each
Need More?	Request Quote

Product Downloads

General

Contents of Kit:

- 1 x UV Curing Pen
- 1 x Li-ion Battery Charger & USB Cable
- 2 x Rechargeable Li-ion Batteries
- 1 x UV Protective Glasses

Physical & Mechanical Properties

Dimensions (mm):

25mm Dia. x 146mm Length

Optical Properties

395.00 **Wavelength (nm):**

7 @ 5mm WD
10 @ 20mm WD **Beam Diameter (mm):**

5 - 20 **Working Distance (mm):**

2 **Irradiance (W/cm²):**

Hardware & Interface Connectivity

1 x Li-ion Battery (Included) **Power Requirement:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

France **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Up to 5.5W/cm² UV Irradiance
- 365nm and 395nm Center Wavelengths
- Available as Wired or Wireless Devices

Handheld UV Curing LED Light Sources provide a range of output powers and beam diameters to best suit the user's application. UV curing pens #17-319 and #20-617 are wireless, handheld, and battery powered devices that provide UV irradiance up to 2W/cm² with up to 2 hours of battery life. UV curing lamps #26-821 and #12-679 are wired, handheld devices that provide adjustable UV irradiance up to 1.4W/cm² or 5.5W/cm² respectively. The wired lamps can be operated through either a button located on the handheld spot light or with an included foot pedal. Handheld UV Curing LED Light Sources are ideal for UV curing, sterilization, or fluorescence of stained gels in optical workshops and laboratories.

Note: Due to the high power of the UV curing lamp #12-679, we recommend using UV Protective Eyewear during operation. Speak with your health and safety manager to ensure you are selecting the proper PPE for your application.