

TECHSPEC®

12.5mm Dia. x 30.0mm FL, NIR II, Inked, Plano-Convex Lens



Stock #38-402-INK 17 TO 22 D= DAYS

[Other Coating Options](#)



1



₹4,394.00

ADD TO CART

Qty 1-9
₹4,394.00
Qty 10+
₹3,959.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 ±0.025

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Back Focal Length BFL (mm): 28.22
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.70 ±0.05
Edge Thickness ET (mm): 1.39
Radius R₁ (mm): 15.51
Clear Aperture CA (mm): 11.5
f#: 2.4
Numerical Aperture NA: 0.21
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View