

TECHSPEC<sup>®</sup> 3mm Dia x 9mm FL Uncoated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#70-885** 20+ In Stock

-

1

+

MRP ₹7,533

 Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹7,533 each                   |
| Qty 6-25       | ₹6,063 each                   |
| Qty 26-49      | ₹5,696 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

Diameter (mm):

|                      |                           |
|----------------------|---------------------------|
| 3.00 +0.00/-0.025    |                           |
| <3                   | Centering (arcmin):       |
| 1.30 ±.05            | Center Thickness CT (mm): |
| 1.02                 | Edge Thickness ET (mm):   |
| 2.5                  | Clear Aperture CA (mm):   |
| Protective as needed | Bevel:                    |

|                    |                                  |
|--------------------|----------------------------------|
| Optical Properties |                                  |
| 9.00               | Effective Focal Length EFL (mm): |
| 8.11               | Back Focal Length BFL (mm):      |
| Uncoated           | Coating:                         |
| Fused Silica       | Substrate: □                     |
| 20-10              | Surface Quality:                 |
| 1.5λ               | Power (P-V) @ 632.8nm:           |
| λ/4                | Irregularity (P-V) @ 632.8nm:    |
| ±1                 | Focal Length Tolerance (%):      |
| 4.13               | Radius R <sub>1</sub> (mm):      |
| 3                  | f/#:                             |
| 0.17               | Numerical Aperture NA:           |
| 200 - 2200         | Wavelength Range (nm):           |

|                                                                                                                                                                                                         |                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| Regulatory Compliance                                                                                                                                                                                   |                             |
| View                                                                                                                                                                                                    | Certificate of Conformance: |
| Italy                                                                                                                                                                                                   | Country of Origin:          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | Imported By:                |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details


- UV-Grade Fused Silica
- Wavelength Range of 200nm to 2.2μm
- Variety of Coating Options Available
- Various Coating Options: [MgF<sub>2</sub>](#), [UV-AR](#), [UV-VIS](#), [VIS-EXT](#), [VIS-NIR](#), [VIS 0°](#), [YAG-BBAR](#), [NIR I](#), and [NIR II](#)

TECHSPEC® UV Fused Silica Plano-Convex (PCX) Lenses Uncoated feature precision specifications and a [variety of coating options](#) on a broadband substrate. Fused Silica is commonly used in applications from the Ultraviolet (UV) through the Near-Infrared (NIR). Its low index of refraction, low coefficient of thermal expansion, and low inclusion content make it ideal for laser applications and harsh environmental conditions. TECHSPEC® UV Fused Silica Plano-Convex (PCX) Lenses Uncoated feature industry leading diameter and centration specifications, making them ideal for integration into demanding imaging and targeting applications.





## Technical Information






UV FS Transmission Curve



| FUSED SILICA                                                                                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|-----------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div><div>Uncoated Fused Silica<br/>Typical Transmission</div><div></div></div>                     | <p>Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                                                                                                                                                                                              |
| <div><div>Fused Silica with MgF<sub>2</sub> Coating<br/>Typical Transmission</div><div></div></div> | <p>Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 1.75\% @ 400 - 700\text{nm}</math> (N-BK7)</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                 |
| <div><div>Fused Silica with UV-AR Coating<br/>Typical Transmission</div><div></div></div>           | <p>Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.0\% @ 250 - 425\text{nm}</math><br/><math>R_{avg} \leq 0.75\% @ 250 - 425\text{nm}</math><br/><math>R_{avg} \leq 0.5\% @ 370 - 420\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |

|                                                                                                                                                                                                                                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>20040060080010001200</div> <div>Wavelength (nm)</div>                                                                                                                                                                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <div>Fused Silica with UV-VIS Coating</div> <div>Typical Transmission</div> <div></div> <div>20040060080010001200</div> <div>Wavelength (nm)</div>            | <div>Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><math>R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}</math><br/><math>R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}</math></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                   |
| <div>Fused Silica with VIS-EXT Coating</div> <div>Typical Transmission</div> <div></div> <div>20040060080010001200</div> <div>Wavelength (nm)</div>         | <div>Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><math>R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}</math></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                                    |
| <div>Fused Silica with VIS-NIR Coating</div> <div>Typical Transmission</div> <div></div> <div>2004006008001000120014001600</div> <div>Wavelength (nm)</div> | <div>Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><math>R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}</math><br/><math>R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}</math><br/><math>R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}</math></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div> |
| <div>Fused Silica with VIS 0° Coating</div> <div>Typical Transmission</div> <div></div> <div>20040060080010001200</div> <div>Wavelength (nm)</div>          | <div>Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><math>R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}</math></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                                     |

|                                                                                                                                                                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div><div>Fused Silica with YAG-BBAR Coating</div><div>Typical Transmission</div><div></div></div> | <div><div>Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.</div><div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div><div><div><math>R_{abs} \leq 0.25\% \text{ @ } 532\text{nm}</math><br/><math>R_{abs} \leq 0.25\% \text{ @ } 1064\text{nm}</math><br/><math>R_{avg} \leq 1.0\% \text{ @ } 500 - 1100\text{nm}</math></div></div><div>Data outside this range is not guaranteed and is for reference only.</div><div><a href="#">Click Here to Download Data</a></div></div>           |
| <div><div>Fused Silica with NIR I Coating</div><div>Typical Transmission</div><div></div></div>   | <div><div>Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.</div><div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div><div><math>R_{avg} \leq 0.5\% \text{ @ } 600 - 1050\text{nm}</math></div><div>Data outside this range is not guaranteed and is for reference only.</div><div><a href="#">Click Here to Download Data</a></div></div>                                                                                                                                                  |
| <div><div>Fused Silica with NIR II Coating</div><div>Typical Transmission</div><div></div></div> | <div><div>Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.</div><div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div><div><div><math>R_{abs} \leq 1.5\% \text{ @ } 750 - 800\text{nm}</math><br/><math>R_{abs} \leq 1.0\% \text{ @ } 800 - 1550\text{nm}</math><br/><math>R_{avg} \leq 0.7\% \text{ @ } 750 - 1550\text{nm}</math></div></div><div>Data outside this range is not guaranteed and is for reference only.</div><div><a href="#">Click Here to Download Data</a></div></div> |