

**TECHSPEC® 3" Dia, 6" FL Protected Alum., Spherical Mirror**



Stock #32-827 **2 In Stock**

- 1 + MRP ₹27,140

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹27,140 each
Qty 10-25	₹23,003 each
Qty 26-49	₹21,692 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Spherical Mirror **Type:**

**Physical & Mechanical Properties**

76.20 +1.0/-0 **Diameter (mm):**

Ground **Back Surface:**

3.0	<b>Diameter (inches):</b>
+0.04/-0	<b>Diameter Tolerance (inches):</b>
0.50	<b>Edge Thickness ET (inches):</b>
12.70	<b>Edge Thickness ET (mm):</b>
+0.0/-15	<b>Edge Thickness Tolerance (%):</b>

## Optical Properties

Metal	<b>Coating Type:</b>
Protected Aluminum (400-2000nm)	<b>Coating:</b>
400 - 2000	<b>Wavelength Range (nm):</b>
152.40	<b>Effective Focal Length EFL (mm):</b>
BOROFLOAT®	<b>Substrate:</b> <input type="checkbox"/>
f/2	<b>Aperture (f/#):</b>
R <sub>avg</sub> >85% @ 400 - 700nm R <sub>avg</sub> >90% @ 400 - 2000nm	<b>Coating Specification:</b>
6.00	<b>Effective Focal Length EFL (inches):</b>
±2	<b>Focal Length Tolerance (%):</b>
λ/4	<b>Surface Accuracy:</b>
60-40	<b>Surface Quality:</b>
0.3 J/cm <sup>2</sup> @ 532nm & 1064nm, 10ns	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>
304.80	<b>Radius of Curvature (mm):</b>

## Regulatory Compliance

Compliant	<b>RoHS 2015:</b>
View	<b>Certificate of Conformance:</b>
Compliant	<b>Reach 247:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Ideal for Multispectral Focusing Applications
- Variety of Coating Options Offered
- Multiple Sizes Available
- [λ/8 Precision Spherical Mirrors](#) Also Available

TECHSPEC® λ/4 Precision Spherical Mirrors are ideal for light collection in multispectral imaging applications. These mirrors are available in a wide range of metallic coating options covering the UV, VIS, and IR spectrum. A BOROFLOAT® substrate provides a good combination of performance and value. TECHSPEC® λ/4 Precision Spherical Mirrors are available in diameters ranging from 25.4 to 152.4mm for ease of system integration. These mirrors

collect and focus light without introducing chromatic aberration.

## Technical Information



;