

TECHSPEC® 3" Dia. Protected Aluminum, $\lambda/10$ Flat ZERODUR®



Stock #31-391-522 **1 In Stock**

⊖ 1 ⊕ MRP ₹73,650

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹73,650 each
Qty 11-25	₹65,579 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror **Type:**

Flatness is specified as Peak to Valley **Note:**

Physical & Mechanical Properties

Diameter (mm):

76.20 +0.0/-1.0

Thickness (mm):

19.10 ±1.5

Back Surface:

Commercial Polish

Clear Aperture CA (mm):

68.58

Optical Properties

Wavelength Range (µm):

0.4 - 2

Coating Type:

Metal

Coating:

Protected Aluminum (400-2000nm)

Surface Flatness (P-V):

λ/10

Wavelength Range (nm):

400 - 2000

Substrate:

ZERODUR®

Coating Specification:

R_{avg} >85% @ 400 - 700nm
R_{avg} >90% @ 400 - 2000nm

Surface Quality:

60-40

Damage Threshold, Reference:

0.3 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Fused Silica and ZERODUR® Substrates
- λ/10 and λ/20 Surface Flatness
- Variety of Coating Options Offered

TECHSPEC® Precision Optical Flat Mirrors are ideal for various applications, including interferometry, imaging systems, laser applications, optical path folding, and autocollimation. These mirrors are available in multiple coating and substrate options and surface flatness options of λ/10 and λ/20. The first substrate option ZERODUR®, a yellow-tinted glass ceramic, features an extremely low coefficient of thermal expansion. TECHSPEC® Precision Optical Flat Mirrors are ideal for applications where temperature fluctuation is a concern using the ZERODUR® substrate. The second option, Fused Silica, is optically clear and features excellent resistance to abrasion and high durability, making it the best choice for applications in harsh environments. Please note, calibration certificates are not supplied with these parts.

TECHSPEC® λ/10 and λ/20 Precision Optical Flats are available for testing and measurement applications.

Note: Surface flatness specifications are measured before coating.

Compatible Mounts

