

[See all 21 Products in Family](#)

## 4-10mm FL, C-Mount, P-Iris, IR Cut Standard Lens



Image represents #22-825; Design will vary by stock number.



Stock **#22-818** **1 In Stock**

1  MRP ₹72,671

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹72,671 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

Varifocal Lens **Type:**

### Physical & Mechanical Properties

P-iris **Iris Option:**

51.50 **Length (mm):**

Not Specified **Maximum Diameter (mm):**

78 **Weight (g):**

## Optical Properties

**Horizontal Field of View @ Max Sensor Format:**  
112 - 44

4-10 **Focal Length Range (mm):**

Not Specified **Working Distance (mm):**

F/1.4 to closed **Aperture (f/#):**

VIS **Lens Wavelength Range:**

## Sensor

1/1.7" **Maximum Sensor Format:**

## Threading & Mounting

C-Mount **Mount:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

Indonesia **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.