


4" x 5", Uncoated Plastic Acrylic Window



Stock **#19-639** 20+ In Stock

-

1

+

₹3,282

ADD TO CART

Volume Pricing	
Qty 1-5	₹3,282 each
Qty 6-24	₹2,641 each
Qty 25-49	₹2,457 each
Need More?	Request Quote

Product Downloads

General

Protective Window

Type:

Physical & Mechanical Properties

91.44 x 114.30

Clear Aperture CA (mm):

4.00 x 5.00 ±0.010

Dimensions (inches):

101.6 x 127.0 ±0.254	Dimensions (mm):
0.06	Thickness (inches):
1.52 ±0.1	Thickness (mm):
101.60	Length (mm):
127.00	Width (mm):
Protective as needed	Bevel:
Smooth, Machined	Edges:

Optical Properties

Uncoated	Coating:
PMMA	Substrate: ☐
1.49	Index of Refraction (n _d):
58	Abbe Number (v _d):
400 - 1600	Wavelength Range (nm):

Material Properties

60	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
----	--

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Highly Scratch-Resistant
 - High Visible Light Transmission
 - Cost-Effective Alternative to Glass
 - [Polycarbonate Plastic Windows](#) Also Available
- Acrylic (PMMA) Plastic Windows are ideal for integration into lightweight optical systems. Compared to polycarbonate windows, acrylic windows are more scratch resistant and can be polished to restore optical quality but are more likely to chip or shatter. Acrylic (PMMA) Plastic Windows also provide a higher UV light transmission than polycarbonate and are recyclable. Acrylic windows are used in a wide variety of industrial and medical applications including aircraft windows, automobile headlights, and ophthalmological devices.

Technical Information

