

[See all 28 Products in Family](#)

4.0 OD, 25mm Dia., Precision Anti-Reflection (AR) Coated Absorptive ND Filter



Precision Absorptive Neutral Density (ND) Filters

Stock **#16-075** **2 In Stock**

-

1

+

₹8,096

ADD TO CART

Volume Pricing	
Qty 1-10	₹8,096 each
Qty 11-25	₹7,318 each
Qty 26-49	₹6,617 each
Need More?	Request Quote

Product Downloads

General	
Neutral Density Filter	Type:
Physical & Mechanical Properties	
25.00	Diameter (mm):
2.82 (nominal)	Thickness (mm):


90	Clear Aperture (%):
<30	Parallelism (arcsec):
Optical Properties	
4.0 ±10% @ 550nm	Optical Density OD (Average):
SCHOTT NG9	Glass/Filter Number:
ND Filter Glass	Substrate: □
BBAR (450-700nm)	Coating:
1.51	Index of Refraction (n _d):
80-50	Surface Quality:
0.01	Transmission (%):
400 - 700	Blocking Wavelength Range (nm):
λ/4	Transmitted Wavefront, P-V:
R _{avg} ≤1.0% @ 450 - 700nm @ 0°	Coating Specification:



Material Properties	
470	Transformation Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- λ/4 Transmitted Wavefront Distortion
 - AR Coated for 450 - 700nm
 - Optical Densities from 0.1 to 4.0 Available
 - [Absorptive Neutral Density \(ND\) Filters](#) Also Available
- Precision Anti-Reflection (AR) Coated Absorptive Neutral Density (ND) Filters feature SCHOTT NG Colored Glass substrates that are polished to achieve a transmitted wavefront distortion (TWFD) specification of λ/4. These filters are coated on both surfaces with an anti-reflection (AR) coating from 450 - 700nm, reducing back reflections and enabling filter stacking with less losses and artifacts. Precision Anti-Reflection (AR) Coated Absorptive Neutral Density (ND) Filters are available with optical densities from 0.1 to 4.0 and can be stacked together to achieve custom optical densities to meet application requirements. These neutral density filters are available in 25mm diameter or 50mm square sizes and are ideal for machine vision, imaging, or low power laser applications.

Technical Information





Compatible Mounts