

[See all 12 Products in Family](#)

## 3mm Diameter, Truncated B270 Half-Ball Lens



B270 Half-Ball Lenses

Stock **#21-897** **4 In Stock**

1  MRP ₹3,734

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹3,734 each
Qty 11-25	₹3,153 each
Qty 26-49	₹2,825 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Half-Ball Lens **Type:**

#### Physical & Mechanical Properties

3.00 ±0.1 **Diameter (mm):**

**Center Thickness CT (mm):**

1.20 ±0.15

Radius R (mm):

1.50

## Optical Properties

**B270**

Substrate: □

Uncoated

Coating:

360 - 2700

Wavelength Range (nm):

1.523

Index of Refraction (n<sub>d</sub>):

## Regulatory Compliance

Compliant

RoHS 2015:

Compliant

Reach 224:

[View](#)

Certificate of Conformance:

Germany

Country of Origin:

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Available in Truncated and Extended Geometries
- High Transmission in the Visible and NIR
- Ideal for Cost Sensitive Applications

B270 Half-Ball Lenses feature a molded spherical surface and polished plano surface, facilitating easier mounting compared to ball lenses. The B270 substrates have high transmission from the visible to the near infrared (NIR) and have a similar refractive index to N-BK7, making these lenses an ideal alternative for cost sensitive applications. Each diameter of lens is available in two form factors, truncated (hypo-hemisphere) and extended (hyper-hemisphere), providing options to best meet system mechanical requirements. B270 Half-Ball Lenses are used in high power LED, fiber coupling, endoscopy, microscopy, and laser measurement applications.