

[See all 8 Products in Family](#)

3mW 655nm, Micro LDM Laser Diode



Stock **#57-101** 1 In Stock

-

1

+

₹13,500

ADD TO CART

Volume Pricing	
Qty 1+	₹13,500 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Mean Time To Failures MTTF @ 25° (hours):
≥50,000

Note:
Includes: Users Manual, Warning Label, and Focus Key

Type of Laser:
Diode

Laser Class - CDRH:
IIIa

Physical & Mechanical Properties	
3	Weight (g):
<25	Pointing Accuracy (mrad):
220	Length of Leads (mm):
27.40	Length (mm):
Optical Properties	
655.00	Wavelength (nm):
<40	Beam Size at Nearest Focus (µm):
3 x 1 at Aperture	Beam Diameter (mm):
<0.5	Beam Divergence (mrad):
Red	Color:
50mm - ∞	Focus Range (mm):
Electrical	
<20	Operating Current (mA):
3	Output Power (mW):
±5 at 25°C	Output Power Tolerance (%):
Hardware & Interface Connectivity	
Power Supply: Power Supply Required and Sold Separately. USA: #59-099 Europe: Not Available Japan: #59-099 Korea: #33-771 China: #59-099	
3.5 - 5 VDC	Power Requirement:
red (+), black (-)	Electrical Leads/ Pin Connections:
Free Space	Output Type:
Environmental & Durability Factors	
-10 to +45	Operating Temperature (°C):
-10 to +85	Storage Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
United Kingdom	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- 7mm Housing Diameter
- Focusable
- Low Voltage DC Operation
- Reverse Polarity Protection

Micro LDMLaser Diode Modules feature an extremely compact design that includes automatic power control circuits and focusable optics. The rugged body is low voltage isolated from the drive electronics, removing the need for negative or floating supplies. It has a highly visible red laser output that can be seen in most daylight conditions. Micro LDMLaser Diode Modules' additional features include aspheric lens, elliptical beam, small output beam diameter, and focused spot size. Meet IEC60825 certification, in accordance with CDRH. Applications include alignment/positioning, bar code readers, dimensional scanning, metrology, event detection, robot control, target designation, edge detection, analysis, and security.

Recommended power supply: [#59-099](#)

