

TECHSPEC®

40.0mm Dia. x 40.0mm FL, NIR I Coated, Plano-Convex Lens



Stock **#48-788** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹5,220.00

ADD TO CART

Qty 1-9
₹5,220.00
Qty 10+
₹4,698.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):
40.00 @ 587.6nm

Back Focal Length BFL (mm): 35.13
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 8.70 ±0.10
Edge Thickness ET (mm): 1.50
Radius R₁ (mm): 31.39
Clear Aperture CA (mm): 39
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant