


TECHSPEC®

3X, Ultrafast-Enhanced Silver Canopus® Reflective Beam Expander


 Stock #13-074 **3 In Stock**

- 1 +

MRP ₹70,119

ⓘ Price inclusive of all taxes

[ADD TO CART](#)

TECHSPEC® Canopus™ Reflective Beam Expanders



Volume Pricing	
Qty 1-5	₹70,119 each
Qty 6+	₹62,048 each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
Zemax:zar	eDrawing:eprt
Code V:seq	EO Spec Sheet
Download All	

General

Type: Beam Expander

Style: Fixed Magnification

Physical & Mechanical Properties

Height (mm): 25.4

Length (mm): 72.68

Weight (g): 117

Width (mm): 38.10

Surface Roughness (Å): <50 RMS

Optical Properties

Entrance Aperture (mm): 4

Exit Aperture (mm): 12

Expansion Power: 3X

Substrate: ⓘ Aluminum 6061-T6

Surface Quality: 40-20

Angle of Incidence (°): 0

Coating: Ultrafast-Enhanced Silver

Design Wavelength DWL (nm): Broadband

Wavelength Range (nm): 600 - 1050

Coating Specification:

$R_{avg} > 99\%$ @ 600 - 1000nm, 0°
 $R_s > 99\%$ @ 540 - 1000nm, 45°
 $R_p > 98.5\%$ @ 730 - 870nm, 45°

Damage Threshold, Reference: ⓘ

0.3 J/cm² @ 800nm, 48fs, 1 pulse (typical)
 0.16 J/cm² @ 800nm, 48fs,

Wavefront Error, P-V: ≤λ/10 on-axis for a 1mm Dia. Input Beam

100Hz, 1000 pulses (typical)

GDD Specification: $0 \pm 20\text{fs}^2$ @ 600 - 1050nm

Damage Threshold, Pulsed: 0.3 J/cm² @ 800nm, 48fs, 100Hz, 1 pulse (typical)
0.16 J/cm² @ 800nm, 48fs, 100Hz, 1000 pulses (typical)

Regulatory Compliance

Certificate of Conformance: [View](#)

Country of Origin: United States

Imported By: Edmund Optics India Private Limited
267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: +91-80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- HR Coated for UV, Visible, and IR Applications from 250nm to 10 μ m
- Multiple Reflective Magnifications from 2X to 5X
- Monolithic Design for Reduced Thermal Effects and [Simplified Alignment](#)
- Manufactured Using Patented Diamond Turning Technique

TECHSPEC® Canopus® Reflective Beam Expanders are ideal for applications requiring broadband or achromatic beam expansion and a wide variety of light sources. The all-reflective design enables these beam expanders to be used with a variety of lasers including tunable, ultraviolet, and ultrafast sources, while the innovative design ensures high precision with minimal wavefront distortion. A variety of integrated design elements, including reflective flats, threaded holes, and thru-holes, simplify alignment, mounting, and integration into any laser application. The monolithic design ensures performance and stability independent of changes in temperature. TECHSPEC Canopus Reflective Beam Expanders are available in 2X, 3X, and 5X magnifications, along with coating options for the UV, Visible, and IR spectra.

For more cost sensitive applications, Edmund Optics also offers [TECHSPEC Scorpii® Nd:YAG Beam Expanders](#). For HeNe laser applications, [TECHSPEC Arcturus® HeNe Beam Expanders](#) are available. For applications where rotating optics are acceptable, the [TECHSPEC Vega® Laser Line Beam Expanders](#) and [TECHSPEC Vega® Broadband Beam Expanders](#) are available. For higher precision applications where sliding optics are necessary, please see our [TECHSPEC Draconis® Nd:YAG Laser Line Beam Expanders](#) or [TECHSPEC Draconis® Broadband Beam Expanders](#).

Compatible Light Sources

- UV Lasers (Excimer, Nd:YAG, etc)
- Infrared Lasers (Nd:YAG, CO₂, Quantum Cascade, etc)
- Ultrafast Lasers (Ti:Sapphire, Fiber, etc)
- Tunable Lasers (Ti:Sapphire, Dye, Quantum Cascade, etc)

DISCOVER EDMUND OPTICS®

FIXED LASER BEAM EXPANDERS | [VIEW ALL >>](#)



Technical Information

Related Products



Laser Beam Expanders



Lasers



Reflective Objectives and Beam Expanders

Frequently Purchased Together



#46-144 - 10X Mitutoyo Plan Apo Infinity Corrected Long WD Objective
₹1,21,599

#58-867 - 75/76.2mm English Tapped Platform
₹13,217

#34-721 - 12.5/12.7mm Optic Dia., Compact Kinematic Mount, 3-Screws
₹11,805

#42-347 - 1/4" x 36", Flexible Fiber Optic Light Guide
₹15,824

Resources

Media Type

- Technical Tool
- Application Note
- Video
- FAQ
- Glossary
- Scientific Paper
- Published Article

TECHNICAL TOOL

Gaussian Beams Calculator

APPLICATION NOTE

Gaussian Beam Propagation

VIDEO

How To Align a Monolithic Beam Expander

APPLICATION NOTE

Can A Beam Expander be Used in Reverse?

APPLICATION NOTE

Beam Expander Selection Guide

APPLICATION NOTE

Beam Expander Testing

View More