

[See all 413 Products in Family](#)

TECHSPEC[®] 40.0mm Dia. x 40.0mm FL, VIS-NIR, Inked, Plano-Convex Lens



Stock **#48-663-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

₹7,155

ADD TO CART

Volume Pricing	
Qty 1-9	₹7,155 each
Qty 10-24	₹6,435 each
Qty 25-49	₹5,715 each
Need More?	Request Quote

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

40.00 ±0.025

<1	Centering (arcmin):
8.70 ±0.10	Center Thickness CT (mm):
1.50	Edge Thickness ET (mm):
39	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties

40.00 @ 587.6nm	Effective Focal Length EFL (mm):
35.13	Back Focal Length BFL (mm):
VIS-NIR (400-1000nm)	Coating:
R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm	Coating Specification:
N-SF11	Substrate: □
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
31.39	Radius R ₁ (mm):
1.00	f/#:
0.50	Numerical Aperture NA:
400 - 1000	Wavelength Range (nm):
5 J/cm ² @ 532nm, 10ns	Damage Threshold, By Design: □

Regulatory Compliance

View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- AR Coated to Provide <1.25% Reflectance per Surface for 400 - 1000nm
- <0.25% Reflectance @ 880nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#)

TECHSPEC® VIS-NIR Coated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. Plano-Convex lenses are ideal for a multitude of optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms. TECHSPEC® VIS-NIR Coated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered [uncoated](#) or with broadband anti-reflective (BBAR) coatings, which include [MgF₂](#), [VIS 0°](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#).

These coated lenses are optimized for a wide range of optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms.

Technical Information



N-BK7																									
Uncoated N-BK7 Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>~70</td></tr><tr><td>400</td><td>~92</td></tr><tr><td>600</td><td>~92</td></tr><tr><td>800</td><td>~92</td></tr><tr><td>1000</td><td>~92</td></tr><tr><td>1200</td><td>~92</td></tr><tr><td>1400</td><td>~92</td></tr><tr><td>1600</td><td>~92</td></tr><tr><td>1800</td><td>~92</td></tr><tr><td>2000</td><td>~92</td></tr><tr><td>2200</td><td>~88</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	~70	400	~92	600	~92	800	~92	1000	~92	1200	~92	1400	~92	1600	~92	1800	~92	2000	~92	2200	~88	Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	~70																								
400	~92																								
600	~92																								
800	~92																								
1000	~92																								
1200	~92																								
1400	~92																								
1600	~92																								
1800	~92																								
2000	~92																								
2200	~88																								
N-BK7 with MgF₂ Coating Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>~70</td></tr><tr><td>400</td><td>~95</td></tr><tr><td>600</td><td>~95</td></tr><tr><td>800</td><td>~95</td></tr><tr><td>1000</td><td>~95</td></tr><tr><td>1200</td><td>~95</td></tr><tr><td>1400</td><td>~95</td></tr><tr><td>1600</td><td>~95</td></tr><tr><td>1800</td><td>~95</td></tr><tr><td>2000</td><td>~95</td></tr><tr><td>2200</td><td>~90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	~70	400	~95	600	~95	800	~95	1000	~95	1200	~95	1400	~95	1600	~95	1800	~95	2000	~95	2200	~90	Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	~70																								
400	~95																								
600	~95																								
800	~95																								
1000	~95																								
1200	~95																								
1400	~95																								
1600	~95																								
1800	~95																								
2000	~95																								
2200	~90																								
N-BK7 with VIS-EXT Coating Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>~70</td></tr><tr><td>400</td><td>~98</td></tr><tr><td>600</td><td>~98</td></tr><tr><td>800</td><td>~98</td></tr><tr><td>1000</td><td>~98</td></tr><tr><td>1200</td><td>~98</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	~70	400	~98	600	~98	800	~98	1000	~98	1200	~98	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data										
Wavelength (nm)	Transmission T (%)																								
200	~70																								
400	~98																								
600	~98																								
800	~98																								
1000	~98																								
1200	~98																								
N-BK7 with VIS-NIR Coating																									

Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with YAG-BBAR Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 532\text{nm}$ $R_{abs} \leq 0.25\% @ 1064\text{nm}$ $R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\% @ 750 - 800\text{nm}$ $R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}$ $R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}$ Data outside this range is not guaranteed and is for reference only.



Coating Curves

Compatible Mounts