

TECHSPEC®

40.0mm Dia. x 300.0mm FL, VIS 0° Coated, Plano-Convex Lens



Stock **#48-242** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹5,133.00

ADD TO CART

Qty 1-9
₹5,133.00
Qty 10+
₹4,611.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):
300.00 @587.6nm

Back Focal Length BFL (mm): 296.70
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 5.00 ±0.10
Edge Thickness ET (mm): 3.70
Radius R₁ (mm): 155.04
Clear Aperture CA (mm): 39
f/#: 7.5
Numerical Aperture NA: 0.07
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View