

TECHSPEC[®] 40mm, 60mm Radius, Metric Goniometer



TECHSPEC[®] Goniometers



Stock #66-529

CONTACT US

-

1

+

₹36,675

ADD TO CART

Volume Pricing	
Qty 1-2	₹36,675 each
Qty 3+	₹32,010 each
Need More?	Request Quote

Product Downloads

General

	Type:
Metric	
	Resolution (arcmin):
5	

Physical & Mechanical Properties

Type of Movement:

Goniometer	
40 x40	Stage Size (mm):
±10	Travel (°):
Brass Stage	Construction:
0.5	Leadscrew Pitch (mm):
3	Load Capacity (kg):
60	Radius R (mm):
1.57 x1.57	Stage Size (inches):
0.3	Weight (kg):

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
------------	----------------

Threading & Mounting

(1) M6 x1, (4) M3 x0.5, (8) M2 x0.4	Mounting Threads:
-------------------------------------	-------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details


[Bottom adapter plates](#), sold separately, are required to mount 30mm and 40mm stages to standard breadboards.

- Metric and English Hole Patterns Available
- Stackable for Two-Axis Rotation
- Mechanically Compatible with our [TECHSPEC® Stages](#)

TECHSPEC® Goniometers allow for precise angular adjustment of an object about a fixed point located above the center of the mounting surface. They provide true tip and tilt adjustment of any optical component and are often used to accurately direct lasers and align mirrors in beam steering applications. These goniometers are available in with Metric and English hole patterns. TECHSPEC® Goniometers are available in different plate sizes to accommodate a host of applications. Each size is offered in several radii of movement for easily stacking into two axis configurations. To provide motion about a common point in two different axes, mount goniometer stages with smaller radii on top of those with larger radii of the same stage size.

Each goniometer stage features precision movement along a dovetail design with a vernier scale for high-resolution measurements and movement repeatability. A locking thumbscrew allows each to be held securely in place. 30mm and 40mm goniometer stages are constructed of durable black painted brass, while 70mm goniometer stages are constructed of black anodized aluminum. [Bottom adapter plates](#), sold separately, are required to mount 30mm and 40mm stages to standard breadboards; 70mm stages will mount directly.

Technical Information



	Top Stage															
	30mm Linear Dovetail	30mm Linear	30mm Vertical	30mm Tip/Tilt	30mm Gonimeter	30mm Rotary	40mm Linear Dovetail	40mm Linear	40mm Vertical	40mm Tip/Tilt	40mm Gonimeter	40mm Rotary	65mm Linear Dovetail	65mm Linear	65mm Vertical	65mm Tip/Tilt
Bottom Stage	30mm Linear Dovetail															
	30mm Linear															
	30mm Vertical															
	30mm Tip/Tilt															
	30mm Gonimeter															
	30mm Rotary															
	40mm Linear Dovetail															
	40mm Linear															
	40mm Vertical															
	40mm Tip/Tilt															
	40mm Gonimeter															
	40mm Rotary															
	65mm Linear Dovetail															
	65mm Linear															
	65mm Vertical															
	65mm Tip/Tilt															
	65mm Gonimeter															
	65mm Rotary															
	125mm Linear															
	125mm Vertical															
	125mm Tip/Tilt															
	125mm Rotary															

