

[See all 40 Products in Family](#)

TECHSPEC® 400nm, 50.8mm Dia. x 9.53mm Thickness, Ultrafast Laser Mirror



Stock #26-825 **10 In Stock**

- 1 + MRP ₹33,395

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹33,395 each
Qty 6-25	₹32,285 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

9.53 ±0.20 **Thickness (mm):**

50.80 +0.00/-0.10 **Diameter (mm):**

Clear Aperture (%):

Back Surface:

Commercial Polish

Parallelism (arcmin):

<3

Optical Properties**Substrate:**

Fused Silica (Corning 7980)

Surface Quality:

10-5

Angle of Incidence (°):

45

Coating:

Ultrafast (380-420nm)

Design Wavelength DWL (nm):

400

Wavelength Range (nm):

380 - 420

Surface Flatness (P-V):

λ/8 over 70% CA

Coating Specification:

R_(avg) S & P >99.90% @ 400nm @ 45° AOI
 R_(avg) >99.7% @ 380 - 420nm @ 45° AOI

Coating Type:

Dielectric

GDD Specification:

±10 fs² @ 380 - 420 nm @ 45° AOI (s-pol)
 ±10 fs² @ 380 - 420 nm @ 45° AOI (p-pol)

Environmental & Durability Factors**Durability:**

ML-PRF-13830B

Regulatory Compliance**Certificate of Conformance:**[View](#)**Country of Origin:**

United States

Imported By:

Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- GDD as Low as ±20fs² at Design Wavelength Range
- Greater than 99.9% Reflectivity
- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers

TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors feature a multilayer dielectric coating on fused silica substrates for excellent reflectivity of greater than 99.9%, and low coefficient of thermal expansion, making them ideal for ultrafast beam transport applications. These mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors are ideal for utilizing the first and second harmonic of Ti:sapphire and Yb:doped lasers for applications such as laser machining and welding.

Note: Please [contact us](#) if your application requires a TECHSPEC Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.