


LightPath 356300 | 4mm Dia., 0.66 NA, BBAR (350-600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-677** 10 TO 12 DAYS

- 1 +

₹8,265.00

ADD TO CART

Qty 1-10
₹8,265.00
Qty 11+
₹7,265.00
Volume Pricing
Request Quote

Get Product Downloads
Diameter (mm): 4.00 ±0.015
Effective Focal Length EFL (mm): 2.54 @ 405nm
Numerical Aperture NA:

0.66
Substrate: L-LAL12
Aspheric Design Wavelength (nm): 405
Coating: BBAR (350-600nm)
Coating Specification: R _{abs} <1.0% @ 350 - 600nm
Surface Quality: 40-20
Clear Aperture CA (mm): 3.30
Edge Thickness ET (mm): 0.77
Center Thickness CT (mm): 1.82 ±0.05
f#: 0.76
Bevel: Protective bevel as needed
Lightpath Lens Code: 356300
Type: Aspheric Lens
Wavelength Range (nm): 350 - 600
Working Distance (mm): 1.55
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant