

[See all 17 Products in Family](#)

TECHSPEC® 40mm Dia. Linear Polarizer Film (XP42HE-40)



Stock #71-895 **20+ In Stock**

- 1 + MRP ₹4,490

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹4,490 each
Qty 11-25	₹3,592 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Note:
Polarization axis can be identified as follows:
Circular Parts - Parallel to direction of notch on polarizer
Square Parts - Parallel to mark on protective film
Rectangular Parts - Parallel to first listed dimension

Physical & Mechanical Properties

40.00 +/-0.3	Diameter (mm):
0.40 +/- 0.05	Thickness (mm):

Polarizing Film	Construction:
-----------------	----------------------

Optical Properties

30,000:1 (Nominal at 555nm)	Extinction Ratio:
Polymer Film XP42HE-40	Substrate: □

<p>Transmission (%): Single: 42.6 (nominal @ 555nm), 41.1 (average 420-700nm) Parallel: 36.4 (nominal @ 555nm), 34.0 (average 420-700nm) Crossed: 0.001 (nominal @ 555nm), 0.002 (average 420-700nm)</p>	Transmission (%):
420 - 700	Wavelength Range (nm):

>99.99% (nominal at 555nm)	Polarization Efficiency (%):
----------------------------	-------------------------------------

Environmental & Durability Factors

-10 to +60	Operating Temperature (°C):
------------	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	REACH 241:
---------------------------	-------------------

Germany	Country of Origin:
<p>Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000</p>	Imported By:

Product Details

- Superior 30,000:1 Extinction Ratio
- Excellent Transmission from 420-700nm
- Available in a Range of Sizes
- Custom Sizes Available

TECHSPEC® Ultra-High Contrast Polarizing Film (XP42HE) are designed to produce a 30,000:1 contrast ratio from 420 – 700nm with an excellent transmission of 42.6%. These polarizing films are available in rectangular geometries in a range of sizes. TECHSPEC Ultra-High Contrast Polarizing Film (XP42HE) are easily cut to required geometries using common cutting tools for system integration. Additionally, the 500 x 1000mm version [#24-286](#) and [#71-907](#) are available with an adhesive backing to facilitate incorporation into various applications. These polarizing films are ideal for imaging, metrology, and microscopy applications where contrast sensitivity is paramount.