

[See all 7 Products in Family](#)

40mm Dia. x 100mm FL Uncoated, DCX N-K5 Lens



Stock #32-908

CLEARANCE

20+ In Stock

-

1

+

₹1,736

ADD TO CART

Volume Pricing	
Qty 1+	₹1,736 each
Need More?	Request Quote

Product Downloads

General

Double-Convex Lens

Type:

Physical & Mechanical Properties

40.00 +0.00/-0.10

Diameter (mm):

<1

Centering (arcmin):

8.00 ±0.10

Center Thickness CT (mm):


Edge Thickness ET (mm):

4.09	
39	Clear Aperture CA (mm):
Protective as needed	Bevel:
Optical Properties	
100.00 @587.6nm	Effective Focal Length EFL (mm):
97.34	Back Focal Length BFL (mm):
Uncoated	Coating:
N-K5	Substrate: □
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
2.5	f/#:
0.20	Numerical Aperture NA:
330 - 2500	Wavelength Range (nm):
Regulatory Compliance	
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- N-K5 Substrate
 - Various Anti-Reflection (AR) Coatings
 - PCX and DCX Options Available
- N-K5 Lenses are available in various diameters, focal lengths, as well as Plano-Convex and Double-Convex form factors. Anti-reflective coatings covering the VIS to NIR make these ideal for multiple applications.

Technical Information



Compatible Mounts