

**TECHSPEC® 4.0mm Dia. x 4.0mm FL, YAG-BBAR Coated Plano-Convex Lens**



YAG-BBAR Coated Plano-Convex (PCX) Lenses



Stock **#88-781** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 +

**₹5,829.00**

ADD TO CART

Qty 1-9

₹5,829.00

Qty 10+

₹5,242.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



**Diameter (mm):**  
4.00 +0.0/-0.025

**Effective Focal Length EFL (mm):**

|                                                                                                                                               |
|-----------------------------------------------------------------------------------------------------------------------------------------------|
| 4.00 @ 587.6nm                                                                                                                                |
| <b>Back Focal Length BFL (mm):</b><br>3.06                                                                                                    |
| <b>Coating:</b><br>YAG-BBAR (500-1100nm)                                                                                                      |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.25% @ 532nm<br>R <sub>abs</sub> <0.25% @ 1064nm<br>R <sub>avg</sub> <1.0% @ 500 - 1100nm |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-LASF44</a>                                                                        |
| <b>Surface Quality:</b><br>20-10                                                                                                              |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                                                                         |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                                                                   |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                                                      |
| <b>Centering (arcmin):</b><br>30-45, typical                                                                                                  |
| <b>Center Thickness CT (mm):</b><br>1.70 ±0.05                                                                                                |
| <b>Edge Thickness ET (mm):</b><br>1.00                                                                                                        |
| <b>Radius R<sub>1</sub> (mm):</b><br>3.21                                                                                                     |
| <b>Clear Aperture CA (mm):</b><br>3.6                                                                                                         |
| <b>f/#:</b><br>1                                                                                                                              |
| <b>Numerical Aperture NA:</b><br>0.50                                                                                                         |
| <b>Type:</b><br>Plano-Convex Lens                                                                                                             |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                                   |
| <b>Wavelength Range (nm):</b><br>500 - 1100                                                                                                   |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>5 J/cm² @ 532nm, 10ns                                                         |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |